

# AMEOF225-HAMJZ

AC-DC Converter

## AMEOF225-HAMJZ






The AMEOF225-HAMJZ series is one of Aimtec's compact (2"x4"x1") 225W AC/DC converter with active PFC and is suitable for medical equipment. It features a universal AC input, which also accepts a DC input voltage, is cost-effective, has a high efficiency and high reliability and comes with double or reinforced isolation.


These converters offer excellent EMC and safety performance, which with UL62368-1, ES60601-1 approvals and meets IEC/EN62368-1, GB4943, EN60335-1, IEC/EN61558-1, IEC/EN60601-1 standards and can be widely used in industrial, LED, street light control, security, telecommunications, smart home and medical applications.

### **Features**

- Universal Input: 85 264VAC/120 370VDC
- Active power factor correction
- Low leakage current: 0.1mA max.
- High isolation voltage: 4000VAC
- Output short circuit, over-current, over-voltage, over temperature protection
- Low no-load power consumption of 0.3W
- Suitable for Type BF application
- Approvals UL62368-1, ES60601-1; Designed to meet IEC/EN62368-1, EN60335-1, IEC/EN61558-1 IEC/EN60601-1



Product Training Video (click to open) Application Notes



## Applications



www.Aimtec.com



## Models & Specifications

### Single Output

Model	Input Voltage (VAC/Hz)	Input Voltage (VDC)	Cooling method	Max Output wattage (W)	Output Voltage (V)	Output Voltage Adjustable Range (V)	Max Output Current (A)	Maximum capacitive load (μF)	<b>Efficiency</b> <b>@230VAC</b> Typ. (%)
AMEOF225-12SHAMJZ	85-264/	120-370	Free air	140	12	11.8-12.6	11.67	6000	93
	47-63	120 570	13CFM	225		11.0 12.0	18.75	0000	55
AMEOF225-15SHAMJZ	85-264/	120-370	Free air	140	15	14.7-15.8	9.33	5000	93
AIVIEUF225-155HAIVIJZ	47-63	120-370	13CFM	225	15		15		
	85-264/	120-370	140	24	22 5 25 2	5.83	2200	04	
AMEOF225-24SHAMJZ	47-63		13CFM	225	24	23.5-25.2	9.4	3200	94
	85-264/	Free air	130	27 26.5	26 5 28 4	4.81	2400	94	
AMEOF225-27SHAMJZ	47-63	120-370	13CFM	225	27	26.5-28.4	8.35	2400	94
	85-264/	120.270	Free air	140	25 25 22 27 0	3.88	2000		
AMEOF225-36SHAMJZ	47-63	120-370	13CFM	225	36	35.28-37.8	6.25	2000	94
	85-264/	120.270	Free air	140	48	47.1 50.4	2.91	1600	
AMEOF225-48SHAMJZ	47-63	120-370	13CFM	225		47.1-50.4	4.7		94
	EOF225-54SHAMJZ #Ø 85-264/ 47-63 1	400.070	Free air	140	54	52.5-55.5	2.59	1000	94
AIVIEUF225-54SHAIVIJZ #Ø		120-370 13	13CFM	225			4.17		
Add suffix -E for enclosed nackage (ex_AMEOE225-12SHAMIZ-E is enclosed nackage version)									

Add suffix -F for enclosed package. (ex. AMEOF225-12SHAMJZ-F is enclosed package version)

### Input Specifications

Parameters	Conditions	Typical	Maximum	Units	
In post our work	115VAC		3	А	
Input current	230VAC		2	А	
Inrush current	115VAC, cold start	40		А	
musn current	230VAC, cold start	75		А	
Leekege	240VAC, normal condition		0.1	mA	
Leakage	240VAC, single fault condition		0.5	mA	
Power factor	115VAC, 100% load	≥0.99			
Power lactor	230VAC, 100% load	≥0.95			

#### **Output Specifications**

Parameters	Conditions	Typical	Maximum	Units
Voltage accuracy		±1		%
Line regulation	Full load	±0.5		%
Load regulation	0-100% load	±0.5		%
	12V, 15-100% load		60	mV p-p
	15, 24, 27, 36, 48V, 15-100% load		100	mV p-p
Ripple & Noise*	54V, 15-100% load		200	mV p-p
Ripple & Noise	12V, 0-15% load		120	mV p-p
	15, 24, 27, 36, 48V, 0-15% load		200	mV p-p
	54V, 0-15% load		400	mV p-p
Hold up time	230VAC, Free air convection	≥16		ms
Hold up time	230VAC, 13CFM	≥12		ms



\* Ripple and Noise are measured at 20MHz bandwidth. Open frame models are measured with a 10µF electrolytic capacitor and a 0.1µF ceramic capacitor. Enclosed models are measured with a 47µF electrolytic capacitor and a 0.1µF ceramic capacitor. Please refer to the application note for specific details.

#### **Isolation Specification**

Parameters	Conditions	Typical	Maximum	Units	
Tested I/O voltage	60 sec, leakage ≤ 10mA	≥4000		VAC	
Tested I, O/PE voltage	60 sec, leakage ≤ 10mA	≥1500		VAC	
Resistance I/O*	500VDC	>50		MΩ	
Resistance I, O/PE*	500VDC	>50		MΩ	
MOP I/O		2xMOPP			
MOP I, O/PE		1xMOPP			
* Tostad under $2E+E^{\circ}C$ ambient temperature with relative humidity <0E% and no condensation					

\* Tested under 25±5°C ambient temperature with relative humidity <95% and no condensation.

#### **General Specifications**

Parameters	Conditions	Typical	Maximum	Units	
Protection class	Class II without protective earth connection, Class I with protective earth connection				
Over current protection	Auto recovery, hiccup $\geq 110$			% of lout	
	12Vout, shut down, manual recovery		16	VDC	
	15Vout, shut down, manual recovery		20	VDC	
	24Vout, shut down, manual recovery		32	VDC	
Over voltage protection	27Vout, shut down, manual recovery		35	VDC	
	36Vout, shut down, manual recovery		50	VDC	
	48, 54Vout, shut down, manual recovery		60	VDC	
Short circuit protection	Hiccup, Continuous, Au	ito recovery time <	3S		
Over temperature protection	Shut down, manual recovery after the te	emperature drops b	pelow the threshold	ł	
F	15V	24V/0.25A, Voltage accuracy ±15		cy ±15%	
Fan power	12, 24, 27, 36, 48, 54V	12V/0.5A, Voltage accuracy ±15%		y ±15%	
No-load power consumption		0.5		W	
Operating temperature	See derating graph -40 to +70			°C	
Storage temperature	-40 to +85			°C	
	-40 °C to -30 °C, forced air convection 13CFM	2.0		%/°C	
	+50 °C to +70 °C, forced air convection 13CFM	2.5		%/°C	
Power Derating	+45 °C to +70 °C, free air convection, open frame	2.0		%/°C	
	+40 °C to +70 °C, free air convection, enclosed	2.0		%/°C	
	85VAC to 115VAC	1.0		%/VAC	
emperature coefficient		±0.03		%/°C	
Cooling	Free air convection, forced air convection 13CFM				
to constatta co	Non-condensing, storage	>10	95	% RH	
Humidity	Non-condensing, operating	>20	90	% RH	
Case material	Enclosed package Metal (1100 Aluminum, SUS30		US304)		
Maight	Open frame	175		g	
Neight	Enclosed	260		g	
	Open frame 4.00 x 2.00 x 1.00 inches (101.6 x 50.8 x 25.4 mm)				
Dimensions (L x W x H)	Enclosed 4.07 x 2.44 x 1.46 inches (103.4 x 62.0 x 37.0 mm)				
ИТВЕ	> 300 000 hrs (MIL-HDBK -217F, t=+25°C)				
NOTE: All specifications in this data output load unless otherwise speci	sheet are measured at an ambient temperature of 25°C, h		•	and at rated	





#### Safety Specifications

Parameters						
Agency approvals	cULus UL 62368-1(# With exception of 54Vout model); AMSI/AAMI ES60601-1 V3.1(Ø With exception of 54Vout model)					
	Design to meet IEC/EN62368-1, EN60335-1, IEC/EN61558-1, IEC/EN60601-1, CAN/CSA-C22.2 No.60601-1:14 Ed3, EN60601- 1-2 Ed4, GB4943-1					
		CISPR32 / EN55032, conducted class B				
	EMC - Conducted and radiated emission*	CISPR32 / EN55032, radiated class B with protective earth connection				
		CISPR32 / EN55032, radiated class A without protective earth connection				
Chandauda	EMC - Harmonic current emissions*	IEC 61000-3-2 class D				
Standards	Electrostatic Discharge Immunity	IEC 61000-4-2 Contact ±8KV, Air ±15KV, Criteria A				
	RF, Electromagnetic Field Immunity	IEC 61000-4-3 10V/m, Criteria A				
	Electrical Fast Transient/Burst Immunity	IEC 61000-4-4 ±4KV, Criteria A				
	Surge Immunity	IEC 61000-4-5 L-L ±2KV L-G ±4KV, Criteria A				
	RF, Conducted Disturbance Immunity	IEC 61000-4-6 10Vr.m.s, Criteria A				
	Voltage dips, Short Interruptions Immunity	IEC 61000-4-11 0%, 70%, Criteria B				
* The power supply is considered as a component and will be installed in an end-product. All the EMC tests are performed with the power supply						


mounted on a 1mm thick 360mm x 360mm metal plate. The EMC compliance of the end-product must be reconfirmed.

## Derating












Dimensions

## Open frame model




#### Note:

- It is needed to have ≥ 10mm distance between the product and external components for safety.
- 2. Connect mounting point 1 and 3 to protective earth for Class I system.
- 3. Connect mounting point 1 and 3 together for Class II system.

Pin Output Specifications						
Pin	Function	Connector	Recommended connector			
1	AC Input (N)/ -V Input	JST B3P-VH	JST VHR,			
2	NC	or equivalent	JST SVH-21PT-P1.1			
3	AC Input (L)/ +V Input	or equivalent	or equivalent			
4	- Fan Output	JST B2B-PH-K-S	JST PHR, JST SPH-002T-P0.5S			
5	+ Fan Output	or equivalent	or equivalent			
6	-V Output					
7	-V Output					
8	-V Output	JST B6P-VH	JST VHR, JST SVH-21PT-P1.1			
9	+V Output	or equivalent	or equivalent			
10	+V Output		or equivalent			
11	+V Output					



### Enclosed model



**NOTE: 1.** Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. **2.** Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. **3.** Mechanical drawings and specifications are for reference only. **4.** All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. **5.** Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. **6.** This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. **7.** Warranty is in accordance with Aimtec's standard Terms of Sale available at <u>www.aimtec.com</u>.