25-Way D Male to Male Low Profile Gender Changer





Specifications


Inter Series Connector A: D25
Convert From Positions: 1 Ways
Convert From Gender: Plug
Inter Series Connector B: D25
Convert To Positions: 1 Ways
Convert To Gender: Plug
Current Rating: 5A


Withstanding Voltage : AC 1000V, 5s Insulation Resistance : $1000M\Omega$ 500V DC Operating Temperature : -55° C to $+105^{\circ}$ C


Housing Material : PBT+30%G.F., Blove, UL94V-0

Contact Material : Brass
Finish Contact Plating : Gold Plated

Diagram







Note:

Connector A&B

DB25P Male Solder Type

Insulation: Black

Shell: Fe (SPcc-SD), Nickel Plated

Part Number Table

| Description | Part Number |
|--|-------------|
| 25-Way D Male to Male Low Profile Gender Changer | PSG90324 |

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

