



Mountz FG Precision Preset Torque Screwdriver

SAFEGUARDING AGAINST FASTENING FAILURES

- Poka-yoke torque screwdriver prevents over-torque
- Accuracy and precision delivered for all fastening applications Unmatched quality you can count on
- Calibration life 4x ISO standards (for the FG-8i, FG-20i, FG-40i & FG-125i models)
 Calibration life 2x ISO standards (for the FG-30z models)
- Two year unlimited warranty
- · Lifetime warranty against manufacturer defects







Quality cam-over technology in the palm of your hand

THE STATE-OF-THE-ART PRECISION TORQUE DRIVER

Engineered and assembled in Silicon Valley, the Mountz FG line of precision preset torque screwdrivers are the most advanced hand tools for high-level process and quality control.

When under- or over-torquing puts your products at risk, Mountz cam-over torque screwdrivers deliver the accuracy you need. Mountz cam-over drivers use an internal cam-over mechanism to reduce the risk of operator error by disengaging once torque is reached. Our cam-over technology increases consistency of torque delivered and joint reliability.

Precision and accuracy delivered every time

BREAKTHROUGH ACCURACY AND REPEATABILITY INCREASES OPERATOR CONFIDENCE AND OVERALL QUALITY OF ASSEMBLY


Mountz FG tools stay in calibration 4X longer than the most stringent industry standard (ISO 6789). Engineered with a cam-over mechanism, the poka-yoke screwdriver prevents over torque. You can give Mountz FG tools to any

operator and have the confidence that they will deliver the correct torque, time

after time.

Our unique bearing system eliminates axial (end) and side loads by the operator, increasing consistency of torque delivered and joint reliability.





Preset cam-over torque screwdriver improves productivity

Modern, effective preset torque screwdrivers improve productivity by guaranteeing that the correct torque value is consistently applied to each fastener. Preset torque screwdrivers are ideal for fastening applications where operators repeatedly assemble parts at the same torque setting. A preset screwdriver is similar to setting an alarm clock to signal the achievement of a selected time. The screwdriver is pre-set to the application's required torque value. The tool signals once torque is achieved.

A preset screwdriver doesn't have an external torque adjustment scale. These tools have an internal torque adjustment mechanism for setting the torque value and preset using a hex key and a torque analyzer. The locking mechanism prevents accidental torque setting changes. Once the tool is set the screwdriver's end cap is sealed with a calibration sticker and ready to be used. However, if the preset torque value needs to be changed for new fastening application the flexible tool can easily be adjusted to a new preset torque value.

The last precision torque screwdriver you'll ever need to buy!

We've tested them over millions of cycles in our controlled lab environment and we still can't break them!

It's why we have an industry-leading warranty.

- Mountz FG tools are the only cam-over drivers on the market to offer a two year unlimited warranty. If it breaks in any way, we'll fix it or replace it for free.
- Lifetime guarantee against manufacturing defects.
- Warranty includes a free calibration within the first year.

PRODUCT OVERVIEW

FEATURE	WHAT IS IT?	ADVANTAGE	END USER BENEFIT
Cycles Before Calibration	ISO 6789-1:2017 calls for maximum of 5,000 torque applications	 Exceeds standards Mountz 4x ISO standards: 20,000 cycles before re-calibration 	Longer time on the production lineReduces calibration budget and down time
Consistency	 Lifecycle testing of well over 3 million combined torque applications 	Confidence every tool meets requirements	Reduces need to replace tools/partsLower required tool inventory
Cam-Over Technology	 Eliminate over-torque Limits the amount of force applied 	 Eliminates fastener breakage issues Ensures correct torque is applied 	 Precision and accuracy Error proofing assembly process Safeguards against fastening failures
Handle Flutes	• Sleek 4-flute handle design	• Ergonomic	Sleek and comfortableEasy to clean
Needle Thrust Bearing	Rotary bearing to allow rotation between parts	 Reduces axial load torque dependency Reduces friction influence on tool output Longer life on internal components 	Higher accuracyDurability
Metal End Cap	 Eliminates possibility of damage to end cap 	Durable and doesn't strip out like plastic	Fewer parts need replacementEasier to service
Bit Retention (Universal Bit Holder)	 ¼ inch female hex bit holder that grips any type of bit Patented One Touch bit release 	 Safe and secure No band / spring and captive ball to fall out 	 Better quality and productivity on line Bits don't fall out or into assembly operation
Locking Mechanism	 Double locking mechanism to prevent accidental torque setting change 	Avoids torque setting drift	Longer period before re-calibrationHigher accuracy over time
Preset Tool	 Internal torque adjustment mechanism Non-graduated setting torque tool 	 Tool is set to a designated torque value Correct torque value is consistently applied 	Enhance process reliabilityImprove production qualityIncrease productivityReduce scrap rates

^{*}Calibration life 4x ISO standards (for the FG-8i, FG-20i, FG-40i & FG-125i models)

^{*}Calibration life 2x ISO standards (for the FG-30z models)



MOUNTZ FG PRESET PRECISION HAND SCREWDRIVER LINEUP

MODEL	ITEM NO.	TORQUE RANGES		LABEL	DRIVE		
		AMERICAN	S.I.	COLOR	SIZE	LENGTH	WEIGHT
FG-30z	076805	3-30 ozf.in	2-21 cN.m	Blue	1/4" F/Hex	4.1"	2.8 oz.
FG-30z	076550	3-30 ozf.in	2-21 cN.m	Red	1/4" F/Hex	4.1"	2.8 oz.
FG-30z	076555	3-30 ozf.in	2-21 cN.m	Green	1/4" F/Hex	4.1"	2.8 oz.
FG-30z	076560	3-30 ozf.in	2-21 cN.m	Gold	1/4" F/Hex	4.1"	2.8 oz.
FG-8i	076546	0.8-8 lbf.in	9-90 cN.m	Blue	1/4" F/Hex	5.2"	7.3 oz.
FG-8i	076551	0.8-8 lbf.in	9-90 cN.m	Red	1/4" F/Hex	5.2"	7.3 oz.
FG-8i	076556	0.8-8 lbf.in	9-90 cN.m	Green	1/4" F/Hex	5.2"	7.3 oz.
FG-8i	076561	0.8-8 lbf.in	9-90 cN.m	Gold	1/4" F/Hex	5.2"	7.3 oz.
FG-20i	076547	2-20 lbf.in	22-226 cN.m	Blue	1/4" F/Hex	5.2"	7.3 oz.
FG-20i	076552	2-20 lbf.in	22-226 cN.m	Red	1/4" F/Hex	5.2"	7.3 oz.
FG-20i	076557	2-20 lbf.in	22-226 cN.m	Green	1/4" F/Hex	5.2"	7.3 oz.
FG-20i	076562	2-20 lbf.in	22-226 cN.m	Gold	1/4" F/Hex	5.2"	7.3 oz.
FG-40i*	076548	4-40 lbf.in	0.4-4.5 N.m	Blue	1/4" F/Hex	6.3"	11.5 oz.
FG-40i*	076553	4-40 lbf.in	0.4-4.5 N.m	Red	1/4" F/Hex	6.3"	11.5 oz.
FG-40i*	076558	4-40 lbf.in	0.4-4.5 N.m	Green	1/4" F/Hex	6.3"	11.5 oz.
FG-40i*	076563	4-40 lbf.in	0.4-4.5 N.m	Gold	1/4" F/Hex	6.3"	11.5 oz.
FG-125i*	076549	25–125 lbf.in	2.8-14.1 N.m	Blue	1/4" F/Hex	6.3"	11.5 oz.
FG-125i*	076554	25-125 lbf.in	2.8-14.1 N.m	Red	1/4" F/Hex	6.3"	11.5 oz.
FG-125i*	076559	25-125 lbf.in	2.8-14.1 N.m	Green	1/4" F/Hex	6.3"	11.5 oz.
FG-125i*	076564	25-125 lbf.in	2.8-14.1 N.m	Gold	1/4" F/Hex	6.3"	11.5 oz.

Designed and manufactured to meet or exceed the accuracy and repeatability requirements of ISO 6789: 2017 (+/- 6% of setting).

Color coding labels allows for torque setting identification in manufacturing area.



Tamper-proof internal adjustment. No external adjustment scale—must be preset using a torque analyzer.



*A removable, sliding T-bar is supplied with FG-40i and FG-125i models.

MOUNTZ FG-OWC PRESET PRECISION HAND SCREWDRIVER LINEUP

MODEL	ITEM NO.	TORQUE RANGES		LABEL	DRIVE	. = =	
		AMERICAN	S.I.	COLOR	SIZE	LENGTH	WEIGHT
FG-8i OWC	076586	0.8-8 lbf.in	9-90 cN.m	Blue	1/4" F/Hex	5.2"	7.3 oz.
FG-8i OWC	076591	0.8-8 lbf.in	9-90 cN.m	Red	1/4" F/Hex	5.2"	7.3 oz.
FG-8i OWC	076596	0.8-8 lbf.in	9-90 cN.m	Green	1/4" F/Hex	5.2"	7.3 oz.
FG-8i OWC	076601	0.8-8 lbf.in	9-90 cN.m	Gold	1/4" F/Hex	5.2"	7.3 oz.
FG-20i OWC	076587	2-20 lbf.in	22-226 cN.m	Blue	1/4" F/Hex	5.2"	7.3 oz.
FG-20i OWC	076592	2-20 lbf.in	22-226 cN.m	Red	1/4" F/Hex	5.2"	7.3 oz.
FG-20i OWC	076597	2-20 lbf.in	22-226 cN.m	Green	1/4" F/Hex	5.2"	7.3 oz.
FG-20i OWC	076602	2-20 lbf.in	22-226 cN.m	Gold	1/4" F/Hex	5.2"	7.3 oz.
FG-40i OWC**	076588	4-40 lbf.in	0.4-4.5 N.m	Blue	1/4" F/Hex	6.3"	11.5 oz.
FG-40i OWC**	076593	4-40 lbf.in	0.4-4.5 N.m	Red	1/4" F/Hex	6.3"	11.5 oz.
FG-40i OWC**	076598	4-40 lbf.in	0.4-4.5 N.m	Green	1/4" F/Hex	6.3"	11.5 oz.
FG-40i OWC**	076603	4-40 lbf.in	0.4-4.5 N.m	Gold	1/4" F/Hex	6.3"	11.5 oz.
FG-125i OWC**	076589	25–125 lbf.in	2.8-14.1 N.m	Blue	1/4" F/Hex	6.3"	11.5 oz.
FG-125i OWC**	076594	25–125 lbf.in	2.8-14.1 N.m	Red	1/4" F/Hex	6.3"	11.5 oz.
FG-125i OWC**	076599	25-125 lbf.in	2.8-14.1 N.m	Green	1/4" F/Hex	6.3"	11.5 oz.
FG-125i OWC**	076604	25–125 lbf.in	2.8-14.1 N.m	Gold	1/4" F/Hex	6.3"	11.5 oz.

FG-OWC (ONE WAY-CLUTCH)

A one-way torque clutch system is designed to apply torque in one direction and remains positive (no torque control) in the opposite direction. This allows the tool to be used for easy screw removal. Ideal for maintenance and refurbishing applications and where undoing or loosening screws is required.

Screwdriver is torque limiting and calibrated in the CW direction only

Designed and manufactured to meet or exceed the accuracy and repeatability requirements of ISO 6789: 2017 (+/- 6% of setting).

Color coding labels allows for torque setting identification in manufacturing area.



**A removable, sliding T-bar is supplied with FG-40i OWC and FG-125i OWC models.



Tamper-proof internal adjustment. No external adjustment scale—must be preset using a torque analyzer.

MOUNTZ FG-IFR PRESET PRECISION HAND SCREWDRIVER LINEUP

MODEL	ITEM NO.	TORQUE RANGES		LABEL	DRIVE	LENGTH	WEIGHT
		AMERICAN	S.I.	COLOR	SIZE	LENGTH	WEIGHT
FG-8i IFR	076651	0.8-8 lbf.in	9-90 cN.m	Blue	1/4" F/Hex	5.2"	7.3 oz.
FG-8i IFR	076656	0.8-8 lbf.in	9-90 cN.m	Red	1/4" F/Hex	5.2"	7.3 oz.
FG-8i IFR	076661	0.8-8 lbf.in	9-90 cN.m	Green	1/4" F/Hex	5.2"	7.3 oz.
FG-8i IFR	076666	0.8-8 lbf.in	9-90 cN.m	Gold	1/4" F/Hex	5.2"	7.3 oz.
FG-20i IFR	076652	2-20 lbf.in	22-226 cN.m	Blue	1/4" F/Hex	5.2"	7.3 oz.
FG-20i IFR	076657	2-20 lbf.in	22-226 cN.m	Red	1/4" F/Hex	5.2"	7.3 oz.
FG-20i IFR	076662	2-20 lbf.in	22-226 cN.m	Green	1/4" F/Hex	5.2"	7.3 oz.
FG-20i IFR	076667	2-20 lbf.in	22-226 cN.m	Gold	1/4" F/Hex	5.2"	7.3 oz.
FG-40i IFR***	076653	4-40 lbf.in	0.4-4.5 N.m	Blue	1/4" F/Hex	6.3"	11.5 oz.
FG-40i IFR***	076658	4-40 lbf.in	0.4-4.5 N.m	Red	1/4" F/Hex	6.3"	11.5 oz.
FG-40i IFR***	076663	4-40 lbf.in	0.4-4.5 N.m	Green	1/4" F/Hex	6.3"	11.5 oz.
FG-40i IFR***	076668	4-40 lbf.in	0.4-4.5 N.m	Gold	1/4" F/Hex	6.3"	11.5 oz.
FG-125i IFR***	076654	25–125 lbf.in	2.8-14.1 N.m	Blue	1/4" F/Hex	6.3"	11.5 oz.
FG-125i IFR***	076659	25-125 lbf.in	2.8-14.1 N.m	Red	1/4" F/Hex	6.3"	11.5 oz.
FG-125i IFR***	076664	25-125 lbf.in	2.8-14.1 N.m	Green	1/4" F/Hex	6.3"	11.5 oz.
FG-125i IFR***	076669	25–125 lbf.in	2.8-14.1 N.m	Gold	1/4" F/Hex	6.3"	11.5 oz.

FG-IFR (IMPACT FREE RESETTING)

The FG screwdrivers' design action is such that when the tool reaches its pre-set torque value, the mechanism disengages from the drive, limiting the torque. Further rotation of the screwdriver handle resets the mechanism, ready for the next torquing operation. The FG-IFR models eliminate any slight reaction during resetting.

Designed and manufactured to meet or exceed the accuracy and repeatability requirements of ISO 6789: 2017 (+/- 6% of setting).


Color coding labels allows for torque setting identification in manufacturing area.



***A removable, sliding T-bar is supplied with FG-40i and FG-125i IFR models.



Tamper-proof internal adjustment. No external adjustment scale—must be preset using a torque analyzer.







Mountz, The Torque Tool Specialists®, has been a leader in the torque tool industry for more than 50 years. Engineered in the Silicon Valley and serving the globe, Mountz focuses on delivering high-quality torque products, services, and solutions to ensure customers can always proceed with confidence. We are committed to forging a safer world through precision and accuracy, and by innovating every day.



mountztorque.com

SILICON VALLEY HEADQUARTERS AND SERVICE CENTER

1080 N. 11th St., San Jose, CA 95112 408-292-2214 / M-F 6am-5pm PST

ALABAMA DISTRIBUTION AND SERVICE CENTER

19051 Underwood Road, Foley, AL 3653!

INTERNATIONAL

For inquiries outside of the USA, Canada, and Mexico, please contact international@mountztorque.com Phone: +44 1428 741756