



a time and place...
for everything

Wi-Sys Communications Inc.

WS3915-HR Very Low Power “No Interference” GPS Antenna with Dual SAW High Rejection Filter


Applications:

- ◆ Battery Powered GPS
- ◆ Anti-jam / Mission Critical GPS
- ◆ Military Radios
- ◆ Law Enforcement / Public Safety
- ◆ Container / Asset Tracking



The WS3915-HR Very Low Power “No Interference” GPS Antenna has the industry’s lowest power consumption and best out-of-band filter performance. The WS3915-HR features ESD circuit protection, a patented very low power two-stage low noise amplifier and a dual SAW high rejection filter. It also features a custom designed ceramic patch element that minimizes detuning effects caused by adjacent objects. The WS3915-HR provides the most consistent, clear GPS signal reception while minimizing loss-of-lock in high-RF fields. Housed in a weatherproof magnetic or screw mount enclosure, the WS3915-HR is ideal for most demanding, power critical GPS applications.

WS3915-HR Dimensions



Features:


- ◆ Very high rejection dual SAW filter
- ◆ Patented high performance dual LNA
- ◆ Very low current: 1.3 mA @ 3.3 V (typ.)
- ◆ 20 dB gain @ 5 V (typ.)
- ◆ 3.6 dB low noise figure
- ◆ 15KV ESD circuit protection
- ◆ Wide voltage input range (2.7 - 5 VDC)
- ◆ Weather proof housing



a time and place...
for everything

Wi-Sys Communications Inc. WS3915-HR Very Low Power “No Interference” GPS Antenna

Out-of-band Filter Rejection



Other Wi-Sys Magnet-mount Antenna

WS3910: Low noise, filtered GPS antenna

WS3914: Low current, filtered GPS antenna

WS3911-HR dual filter high rejection GPS antenna

WS3917: Low cost, filtered GPS antenna

WS3942: Active, filtered GPS + Cellular combined antenna

WS3948: Active, filtered GPS + 2.4 GHz combined antenna

Technical Specifications

Environmental Specifications

- ◆ -40c to +80c operating (-45c to +80c storage)
- ◆ IP67 / Weather proof

Mechanical

- ◆ 45mm x 51mm x 12mm
- ◆ 120g (4.2 oz)
- ◆ Attachment methods: Magnetic (5 lb lift-off force) or permanent (pre-threaded for 3 x M2.5 screws)
- ◆ Shock: Vertical axis 50G, other axes 30G
- ◆ Vibration: 3 axis, sweep = 15 min
10 – 200 Hz log sweep: 3G

Antenna Response

- ◆ Frequency: 1575.42 MHz
- ◆ Gain: @ 90° 3 dBic, @ 20° -2.0 dBic
- ◆ Polarization: Right Hand Circular
- ◆ Axial ratio: @ 90° 4 dB, @ 20° 6 dB

Electrical

- ◆ Voltage: 2.7 – 5 VDC
- ◆ Current: 1.3 mA @ 3.3VDC, 2 mA @ 5VDC
- ◆ ESD circuit protection: 15K Volts
- ◆ Cable: 1.5 DS-QEHV Shikoku Cable Co. Ltd.
- ◆ Cable length: 3 metres (standard),
other lengths optional
- ◆ Cable loss: 1.3 dB/m typical
- ◆ Connector: SMA (standard),
other connectors optional

LNA Specifications

- ◆ Frequency: 1572.5 – 1578 MHz
- ◆ Output Impedance: 50 Ohm
- ◆ VSWR: 1.5:1 max (at connector)
- ◆ Gain: 20 dB @ 5VDC (typical)
- ◆ Noise figure: 3.6 dB

Wi-Sys Communications Inc.

31B Richardson Side Road
Ottawa, ON K2K 0A1 Canada
Tel 613.254.7386 Fax 613.254.7388
sales@wi-sys.com www.wi-sys.com

