




Features

- Capable of switch electric circuit with load
- Adaptable to padlock device
- Contact position indication
- Capable of quickly releasing stored energy operation
- Highlighted to high making and breaking capacity
- Used as main switch for household and similar installation

Specifications

Voltage Rating	: 230V AC
Rated Residual Current	: 30mA, 100mA, 300mA
Number of poles	: 2P
Rated frequency	: 50/60Hz
Electrical Endurance	: 10000 Cycles
Mechanical Endurance	: 20000 Cycles
Rated Impulse withstand Voltage	: 6kV
Terminals	: Pillar Type
Cable Termination	: 35mm ²
Torque of Screw	: 3.5Nm
IP Degree	: IP20

Diagram



Dimensions : Millimetres

Part Number Table

Description	Part Number
100A DP Incomer Main Switch Isolator	AUT2

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.