ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

Field Stop Trench IGBT

650 V, 50 A

FGHL50T65MQDTL4

Field stop 4th generation mid speed IGBT technology copacked with full rated current diode.

Features

- Maximum Junction Temperature: $T_J = 175^{\circ}C$
- Positive Temperature Co-efficient for Easy Parallel Operating
- High Current Capability
- Low Saturation Voltage: $V_{CE(Sat)} = 1.45 \text{ V} (Typ.) @ I_C = 50 \text{ A}$
- 100% of the Parts are Tested for ILM (Note 2)
- Smooth and Optimized Switching
- Tight Parameter Distribution
- RoHS Compliant

Typical Applications

- Solar Inverter
- UPS. ESS
- PFC, Converters

MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Collector to Emitter Voltage	V_{CES}	650	V
Gate to Emitter Voltage Transient Gate to Emitter Voltage	V_{GES}	±20 ±30	V
	Ι _C	80 50	A
Pulsed Collector Current (Note 2)	I _{LM}	200	А
Pulsed Collector Current (Note 3)	I _{CM}	200	А
Diode Forward Current (Note 1) @ $T_{C =} 25^{\circ}C$ @ $T_{C =} 100^{\circ}C$	lF	60 50	A
Pulsed Diode Maximum Forward Current	I _{FM}	200	А
$ \begin{array}{ll} \mbox{Maximum Power Dissipation} & @\ T_C = 25^\circ C \\ & @\ T_C = 100^\circ C \end{array} $	P _D	268 134	W
Operating Junction and Storage Temperature Range	T _J , T _{STG}	–55 to +175	°C
Maximum Lead Temp. for Soldering Purposes (1/8" from case for 5 s)	ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. Value limit by bond wire


- 2. V_{CC} = 400 V, V_{GE} = 15 V, I_C = 200 A, Inductive Load, 100% tested
- 3. Repetitive rating: pulse width limited by max. junction temperature



ON Semiconductor®

www.onsemi.com








CASE 340CJ

MARKING DIAGRAM



\$Y

&Z

&3

&K

ORDERING INFORMATION

Device	Package	Shipping
FGHL50T65MQDTL4	TO-247-4LD	30 Units / Tube

THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Thermal resistance junction-to-case, for IGBT	$R_{ extsf{ heta}JC}$	0.56	°C/W
Thermal resistance junction-to-case, for Diode	$R_{ extsf{ heta}JC}$	0.74	°C/W
Thermal resistance junction-to-ambient	$R_{ hetaJA}$	40	°C/W

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)


Parameter	Test Conditions	Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS	•			•	•	
Collector to Emitter Breakdown Voltage	V _{GE} = 0 V, I _C = 1 mA	BV _{CES}	650	-	-	V
Temperature Coefficient of Breakdown Voltage	V _{GE} = 0 V, I _C = 1 mA	$\frac{\Delta BV_{CES}}{\Delta T_{J}}$	_	0.6	-	V/°C
Collector to Emitter Cut-off Current	V _{GE} = 0 V, V _{CE} = 650 V	I _{CES}	-	-	250	μA
Gate Leakage Current	V _{GE} = 20 V, V _{CE} = 0 V	I _{GES}	I	-	±400	nA
ON CHARACTERISTICS						
Gate to Emitter Threshold Voltage	$V_{GE} = V_{CE}, I_C = 50 \text{ mA}$	V _{GE(th)}	3.0	4.5	6.0	V
Collector to Emitter Saturation Voltage	V_{GE} = 15 V, I _C = 50 A, T _J = 25°C V _{GE} = 15 V, I _C = 50 A, T _J = 175°C	V _{CE(sat)}	-	1.45 1.65	1.8 -	V
DYNAMIC CHARACTERISTICS						
Input Capacitance	$V_{CE} = 30 V,$	C _{ies}	-	3335	-	pF
Output Capacitance	V _{GE} = 0 V, f = 1 MHz	C _{oes}	-	105	-	
Reverse Transfer Capacitance		C _{res}	-	11	-	
Gate Charge Total	$V_{CE} = 400 V,$	Qg	-	99	-	nC
Gate to Emitter Charge	I _C = 50 A, V _{GE} = 15 V	Q _{ge}	-	17	-	
Gate to Collector Charge		Q _{gc}	-	24	-	
SWITCHING CHARACTERISTICS, INDUC	TIVE LOAD					
Turn-on Delay Time	$T_J = 25^{\circ}C,$	t _{d(on)}	-	45	-	ns
Rise Time	V _{CC} = 400 V, I _C = 25 A,	t _r	-	18	-	-
Turn-off Delay Time	R _G = 30 Ω, V _{GE} = 15 V	t _{d(off)}	-	360	-	
Fall Time		t _f	-	51	-	1
Turn-on Switching Loss		E _{on}	-	0.44	-	mJ
Turn-off Switching Loss	1	E _{off}	-	0.35	-	
Total Switching Loss		E _{ts}	-	0.79	-	
Turn-on Delay Time	$\begin{array}{c} T_{J}=25^{\circ}C,\\ V_{CC}=400\ V,\\ I_{C}=50\ A,\\ R_{G}=30\ \Omega,\\ V_{GE}=15\ V \end{array}$	t _{d(on)}	-	50	-	ns
Rise Time		t _r	-	27	-	
Turn-off Delay Time		t _{d(off)}	-	336	-	
Fall Time		t _f	-	37	-	
Turn-on Switching Loss	1	E _{on}	-	1.00	-	mJ
Turn-off Switching Loss	1	E _{off}	-	0.85	-	
Total Switching Loss	1	E _{ts}	-	1.85	-	


ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Parameter	Test Conditions	Symbol	Min	Тур	Max	Unit
SWITCHING CHARACTERISTICS, IND	UCTIVE LOAD					
Turn-on Delay Time	$T_{J} = 175^{\circ}C,$	t _{d(on)}	-	40	-	ns
Rise Time	V _{CC} = 400 V, I _C = 25 A,	t _r	-	22	-	1
Turn-off Delay Time	R _G = 30 Ω, V _{GE} = 15 V	t _{d(off)}	-	389	-	1
Fall Time		t _f	-	85	-	1
Turn-on Switching Loss		Eon	-	0.84	-	mJ
Turn-off Switching Loss		E _{off}	-	0.61	-	1
Total Switching Loss		E _{ts}	-	1.45	-	1
Turn-on Delay Time	T _J = 175°C,	t _{d(on)}	-	43	-	ns
Rise Time	V _{CC} = 400 V, I _C = 50 A,	t _r	-	35	-	1
Turn-off Delay Time	R _G = 30 Ω, V _{GE} = 15 V	t _{d(off)}	-	365	_	1
Fall Time	- GE	t _f	-	72	-	1
Turn-on Switching Loss		Eon	-	1.60	-	mJ
Turn-off Switching Loss		E _{off}	-	1.30	-	
Total Switching Loss		E _{ts}	-	2.90	_	
DIODE CHARACTERISTICS						
Diode Forward Voltage	I _F = 50 A, T _J = 25°C	V _F	-	1.65	2.1	V
	I _F = 50 A, Τ _J = 175°C		-	1.55	-	
DIODE SWITCHING CHARACTERISTIC	CS, INDUCTIVE LOAD					
Reverse Recovery Energy	$T_J = 25^{\circ}C$, $V_{CE} = 400$ V, $I_F = 25$ A,	E _{rec}	-	65	-	μJ
Diode Reverse Recovery Time	di _F /dt = 1000 A/µs	T _{rr}	-	44	-	ns
Diode Reverse Recovery Charge		Q _{rr}	-	387	-	nC
Diode Reverse Recovery Current		I _{rr}	-	18	-	Α
Reverse Recovery Energy	$T_J = 25^{\circ}C, V_{CE} = 400 V, I_F = 50 A,$	E _{rec}	-	128	-	μJ
Diode Reverse Recovery Time	di _F /dt = 1000 A/μs	T _{rr}	-	79	-	ns
Diode Reverse Recovery Charge		Q _{rr}	-	681	-	nC
Diode Reverse Recovery Current		I _{rr}	-	17	-	Α
Reverse Recovery Energy	T _J = 175°C, V _{CE} = 400 V, I _F = 25 A,	E _{rec}	-	380	-	μJ
Diode Reverse Recovery Time	— di _F /dt = 1000 A/μs	T _{rr}	-	102	-	ns
Diode Reverse Recovery Charge		Q _{rr}	-	1482	-	nC
Diode Reverse Recovery Current		I _{rr}	-	29	-	Α
Reverse Recovery Energy	$T_{J} = 175^{\circ}C, V_{CE} = 400 V, I_{F} = 50 A,$	E _{rec}	-	544	-	μJ
Diode Reverse Recovery Time	di _F /dt = 1000 A/μs	T _{rr}	-	135	_	ns
Diode Reverse Recovery Charge	7	Q _{rr}	-	2023	-	nC
Diode Reverse Recovery Current	1	I _{rr}	_	30	_	Α

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS












Figure 3. Typical Saturation Voltage Characteristics










Figure 4. Typical Transfer Characteristics





TYPICAL CHARACTERISTICS (continued)






Figure 9. Turn-on Characteristics vs. Gate Resistance




Figure 10. Turn-off Characteristics vs. Gate Resistance





Figure 11. Turn-on Characteristics vs. Collector Current Figure 12. Turn-off Characteristics vs. Collector Current

TYPICAL CHARACTERISTICS (continued)



TYPICAL CHARACTERISTICS (continued)





Figure 20. Transient Thermal Impedance of Diode

PACKAGE DIMENSIONS

TO-247-4LD CASE 340CJ **ISSUE A**



NOTES:

A. NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
B. DIMENSIONS ARE EXCLUSIVE OF BURRS,MOLD FLASH,AND TIE BAR EXTRUSIONS.
C. ALL DIMENSIONS ARE IN MILLIMETERS.
D. DRAWING CONFORMS TO ASME Y14.5-2009.

	1				
DIM	MILLIMETERS				
	MIN	NOM	MAX		
А	4.80	5.00	5.20		
A1	2.10	2.40	2.70		
A2	1.80	2.00	2.20		
b	1.07	1.20	1.33		
b1	1.20	1.40	1.60		
b2	2.02	2.22	2.42		
С	0.50	0.60	0.70		
D	22.34	22.54	22.74		
D1	16.00	16.25	16.50		
D2	0.97	1.17	1.37		
е	2	2.54 BSC			
e1	Ę	5.08 BSC)		
Е	15.40	15.60	15.80		
E1	12.80	13.00	13.20		
E/2	4.80	5.00	5.20		
L	18.22	18.42	18.62		
L1	2.42	2.62	2.82		
р	3.40	3.60	3.80		
р1	6.60	6.80	7.00		
Q	5.97	6.17	6.37		
S	5.97	6.17	6.37		

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor hy such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, a

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative