



SAFETY DATA SHEET

according to Regulation (EU) 2015/830

Page 1/6

Screen Wash -15

Revision 2

Revision date 2019-07-08

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	Screen Wash -15
--------------	-----------------

1.2. Relevant identified uses of the substance or mixture and uses advised against

Product Use	[SU21] Consumer uses: Private households (= general public = consumers); ----- [SU22] Professional uses: Public domain (administration, education, entertainment, services, craftsmen);
Description	Screen Wash.

1.3. Details of the supplier of the safety data sheet

Company	Future Developments Manufacturing Ltd
Address	Davenport Street Burslem Stoke on Trent ST6 4HS Staffordshire
Web	www.fdev.co.uk
Telephone	01782 826870
Email	sales@fdev.co.uk
Email address of the competent person	support@fdhost.co.uk

1.4. Emergency telephone number

Emergency telephone number	01782 829000 9.00am-5.00pm Mon - Fri
----------------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

2.1.2. Classification - EC 1272/2008	Flam. Liq. 3: H226;
--------------------------------------	---------------------

2.2. Label elements

Hazard pictograms	
Signal Word	Warning
Hazard Statement	Flam. Liq. 3: H226 - Flammable liquid and vapour.
Precautionary Statement: Prevention	P102 - Keep out of reach of children P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P233 - Keep container tightly closed.

Screen Wash -15

Revision 2

Revision date 2019-07-08

2.2. Label elements

Precautionary Statement: Response	P240 - Ground/bond container and receiving equipment. P241 - Use explosion-proof electrical/ventilating/lighting// equipment. P242 - Use only non-sparking tools. P243 - Take precautionary measures against static discharge. P280 - Wear protective gloves/protective clothing/eye protection/face protection.
Precautionary Statement: Storage	P303+P361+P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. P370+P378 - In case of fire: Use to extinguish.
Precautionary Statement: Disposal	P403+P235 - Store in a well-ventilated place. Keep cool. P501 - Dispose of contents/container to local and national regulations

SECTION 3: Composition/information on ingredients

3.2. Mixtures

EC 1272/2008

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Ethanol	603-002-00-5	64-17-5	200-578-6		10 - 20%	Flam. Liq. 2: H225;

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	No precautions required to be mentioned.
Eye contact	May cause irritation to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
Skin contact	May cause irritation to skin. Wash off immediately with plenty of soap and water. Remove contaminated clothing. Seek medical attention if irritation or symptoms persist.
Ingestion	Ingestion may cause nausea and vomiting. Seek medical attention if irritation or symptoms persist.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	See section 4.1 for further information.
Eye contact	See section 4.1 for further information.
Skin contact	See section 4.1 for further information.
Ingestion	See section 4.1 for further information.

General information

	In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).
--	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
--	---

5.2. Special hazards arising from the substance or mixture

	. Burning produces irritating, toxic and obnoxious fumes.
--	---

5.3. Advice for firefighters

	Wear suitable respiratory equipment when necessary.
--	---

Screen Wash -15

Revision 2

Revision date 2019-07-08

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

	Ensure adequate ventilation of the working area. Evacuate personnel to a safe area. Eliminate all sources of ignition. Wear suitable protective equipment.
--	--

6.2. Environmental precautions

	Do not allow product to enter drains. Prevent further spillage if safe.
--	---

6.3. Methods and material for containment and cleaning up

	Absorb with inert, absorbent material. Transfer to suitable, labelled containers for disposal. Clean spillage area thoroughly with plenty of water.
--	---

6.4. Reference to other sections

	See section 2,3,8,13 for further information.
--	---

SECTION 7: Handling and storage

7.1. Precautions for safe handling

	Avoid contact with eyes and skin. Ensure adequate ventilation of the working area. Use explosion proof equipment. Keep away from sources of ignition - No smoking.
--	--

7.2. Conditions for safe storage, including any incompatibilities

	Keep in a cool, dry, well ventilated area. Keep containers tightly closed. Store in correctly labelled containers.
--	--

7.3. Specific end use(s)

	See section 1.2 for further information.
--	--

SECTION 8: Exposure controls/personal protection


8.1. Control parameters

	See section 8.2 for further information.
--	--

8.1.1. Exposure Limit Values

Ethanol	WEL 8-hr limit ppm: 1000	WEL 8-hr limit mg/m3: 1920
	WEL 15 min limit ppm: -	WEL 15 min limit mg/m3: -
	WEL 8-hr limit mg/m3 total -	WEL 15 min limit mg/m3 total -
	inhalable dust:	inhalable dust:
	WEL 8-hr limit mg/m3 total -	WEL 15 min limit mg/m3 total -
	respirable dust:	respirable dust:

8.2. Exposure controls

	
8.2.1. Appropriate engineering controls	SPILLAGE MAY CREATE SLIP HAZARD.
8.2.2. Individual protection measures	Wear chemical protective clothing.

Screen Wash -15

Revision 2

Revision date 2019-07-08

8.2. Exposure controls

Eye / face protection	Approved safety goggles.
Skin protection - Handprotection	Chemical resistant gloves (PVC).

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Various
Odour	Characteristic
pH	7 - 8
Melting point	Not applicable.
Freezing Point	-10
Initial boiling point	Not applicable.
Flash point	39 °C
Evaporation rate	Not applicable.
Flammability (solid, gas)	Not applicable.
Relative density	Not applicable.
Fat Solubility	Not applicable.
Partition coefficient	Not applicable.
Autoignition temperature	Not applicable.
Viscosity	Not applicable.
Explosive properties	Not applicable.
Oxidising properties	Not applicable.
Solubility	Soluble in water

9.2. Other information

Conductivity	Not applicable.
Surface tension	Not applicable.

SECTION 10: Stability and reactivity

10.1. Reactivity

	Stable under recommended storage conditions.
--	--

10.2. Chemical stability

	Stable under normal conditions.
--	---------------------------------

10.3. Possibility of hazardous reactions

	Oxidising agents.
--	-------------------

10.4. Conditions to avoid

	Heat, sparks and open flames.
--	-------------------------------

10.5. Incompatible materials

	No data available.
--	--------------------

10.6. Hazardous decomposition products

	No data is available on this product.
--	---------------------------------------

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Skin corrosion/irritation	May cause mild skin irritation.
Serious eye damage/irritation	There may be mild irritation.

Screen Wash -15

Revision 2

Revision date 2019-07-08

11.1.4. Toxicological Information

No data available

SECTION 12: Ecological information

12.1. Toxicity

No data available

12.2. Persistence and degradability

No data is available on this product.

12.3. Bioaccumulative potential

Partition coefficient

Michelin Screen Wash -10 Not applicable.

12.4. Mobility in soil

No data is available on this product.

12.5. Results of PBT and vPvB assessment

No data is available on this product.

12.6. Other adverse effects

However, large or frequent spills may have hazardous effects on the environment. The product is not regarded as dangerous for the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local requirements. Do NOT incinerate the container even when empty.

General information

Dispose of in compliance with all local and national regulations.

SECTION 14: Transport information

Hazard pictograms



14.1. UN number

UN1993

14.2. UN proper shipping name

FLAMMABLE LIQUID, N.O.S.

14.3. Transport hazard class(es)

ADR/RID	3
Subsidiary risk	-
IMDG	3
Subsidiary risk	-
IATA	3
Subsidiary risk	-

Screen Wash -15

Revision 2

Revision date 2019-07-08

14.4. Packing group

Packing group	III
---------------	-----

14.5. Environmental hazards

Environmental hazards	No
Marine pollutant	No

ADR/RID

Hazard ID	30
Tunnel Category	(D/E)

IMDG

EmS Code	F-E S-E
----------	---------

IATA

Packing Instruction (Cargo)	366
Maximum quantity	220 L
Packing Instruction (Passenger)	355
Maximum quantity	60 L

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

	The classification detailed on this safety data sheet refers to the neat material only. Dilution of the product may reduce the classification. This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006 & (EC) No. 1272/2008 & (EC) 1999/45.
--	--

15.2. Chemical safety assessment

	No information available.
--	---------------------------

SECTION 16: Other information

Other information

Revision	This document differs from the previous version in the following areas:. 12 - 12.1. Toxicity.
Text of Hazard Statements in Section 3	Flam. Liq. 2: H225 - Highly flammable liquid and vapour.

Further information

	The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.
--	--