



Tango 39

433MHz ISM band panel mounting puck Antenna



Key Features

- 433MHz ISM band frequency
- Compact puck design
- 1dBi Peak Gain
- TETRA Compatible

General Description

The Tango 39 is a very compact puck shaped antenna tuned to the 433MHz ISM band.

Typical applications are garage remote control systems, TETRA Radio Systems, property alarms, wireless sensor connections and LoRa EU433 IoT device connections.

The antenna is supplied as standard with an SMA male connector on 1m of cable. Alternative connectors and cable lengths can be supplied for volume orders.

Additional Considerations

- Weather resistant antenna
- Suitable for unlicensed band based applications



Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW +44(0)118 976 9000 sales@siretta.com www.siretta.com

sales

email

web





Tango 39

433MHz ISM band panel mounting puck Antenna


Mechanical Specifications


Electrical Specifications

Impedance:	50 Ohm
VSWR:	≤1.5:1
Peak Gain:	1dBi
Frequency Range:	433MHz
Bandwidth:	10MHz
Power Capactity:	50W
Polarization:	Vertical

Operating temperature:	-30 - +75°C
Storage temperature:	-30 - +75°C
Dimensions:	46 Ø x 15mm
Cable:	RG174
Connector:	SMA Male
Mounting Method:	M12mm

Test Curve





Ordering Details

Part Number	Description
TANGO39/1M/SMAM/S/S/17	433MHz ISM band panel mounting puck Antenna 1M SMA Male
TANGO39/1M/SMAM/S/S/17	433MHz ISM band panel mounting puck Antenna 2.5m SMA Male

Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW sales

email

web

+44(0)118 976 9000 sales@siretta.com www.siretta.com