


**ELECTRICAL TEST:**



- 1.100% OPEN SHORT MIS WIRE TEST
- 2.CONTACT RESISTANCE:3 OHM MAX
- 3.INSULATION RESISTANCE:5M OHM MIN
- 4.HI-POT TEST:DC 300V/10ms
- 5.PASS 8K@60Hz TEST

JIB Article No	LENGTH(mm)
3M	3000±30



**PIN Assignment**

**P1 HDMI AM      P2 HDMI AM**



⑥	Cable	(1/0.34BC*1P+D1/0.254TC+AL-Foil+ADHESIVE-PET)*5C+1/0.254BC*3C+1/0.32BC*1C+AL-Foil+D7/0.16TC+160#/0.12AL BLACK PVC Jacket OD:7.3±0.15mm	M
⑤	outer molding	BLACK PVC 45P	xxg
④	inner molding	PE,Nature color	xxg
③	Copper foil	Copper foil size:5mm	mm
②	SHELL	Silver aluminum shell	2PCS
①	Connector	HDMI AM 19P SHELL/PIN:Gold plated & Tinplate	2PCS
NO.	PART NAME	DESCRIPTION	UNIT

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.		△			
		YAN	YAN	FINISHING		△	2021/07/09		A1
				MATERIAL		SYM	DATE		REVISION