

Models Available

TFDRMU Digital Multifunction Timer 24-240Vac/dc

Product Features

- 4 digit backlit LCD display digital timer
- 24 programmable timing modes
- 0-9999sec or 0-9999min time ranges
- 24 to 240Vac/dc powered
- 1 changeover and 1 N/O relay output
- Easy to programme through front keys
- Status and timing indicators
- EEPROM memory (minimum 10 years)
- IP20 enclosure code
- DIN rail mounting
- 2 module 36mm width
- Clear hinged tamperproof cover

TFDRMU Digital Multifunction Timer


The Tempatron TFDRMU digital timer is a 4 digit multifunction, multi-time range timer suitable for controlling the operation of equipment, machinery, systems or processes in a wide range of industrial applications.

This dual digital timer has two relay outputs which can be configured as two independent timed outputs. A choice of 24 timing function modes can be selected for each of the outputs, together with a time range from 1 second to 9999 minutes. The output contacts are fully isolated from the supply voltage.


These timers are housed in a compact DIN rail mounting enclosure measuring only 36mm in width and are powered from a wide range of 24 to 240Vac/dc.

For timing control of machinery, systems and operational processes

Dimensions



Connections




Continued...

Timing Mode	Timing Function Description	Start Mode	
Mode 01	Delay on Energise (On Delay)	Starts when power applied	
	, , , , ,		
Mode 02	Interval	Starts when power applied	
Mode 03	Delayed Cycling with Equal On and Off Time	Starts when power applied	
Mode 04	Immediate Cycling with Equal On and Off Time Starts when power applied		
Mode 05	Delayed Pulse (0.5 second)	Starts when power applied	
Mode 06	Interval (Close to Start)	Close to Start	
Mode 07	Interval (Open to Start)	Open to Start	
Mode 08	Delay On Delay Off	Close to Start	
Mode 09	Bistable with Time Limit	Close to Start, Close again to Stop	
Mode 10	Delay on De-Energise (Re-triggerable)	Close to Start, Open for Time Delay	
Mode 11	Delay on De-Energise (Non re-triggerable)	Close to Start, Open for Time Delay	
Mode 12	Delay on Energise	Pulse to Start	
Mode 13	Output Permanently On	tly On Starts when power applied	
Mode 14	Output Permanently Off	Starts when power applied	
Mode 15	Single Delayed Cycle with Variable On and Off Times	Starts when power applied	
Mode 16	Single Immediate Cycle with Variable On and Off Times	es Starts when power applied	
Mode 17	Delayed Cycling with Variable On and Off Times Starts when power applied		
Mode 18	Immediate Cycling with Variable On and Off Times Starts when power applied		
Mode 19	Delay On Delay Off with Variable Off and On Times	ff and On Times Close to Start (Re-triggerable)	
Mode 20	Delay On Delay Off with Variable Off and On Times	Close to Start (Non Re-triggerable)	
Mode 21	Interval with Alternate Time Duration	Close to Start	
Mode 22	Delay Off Delay On	Close to Start	
Mode 23	Delay on Energise followed by Independent Interval	val Close to Start	
Mode 24	Interval followed by Independent Delay on De-Energise	Close to Start	

Email: sales@tempatron.co.uk

Front Panel Display Functions



Ordering information

Model	Code	Description
	TFDRMU	DIN Rail Mounting Digital Multifunction Timer
		24 to 240Vac/dc
Example	TFDRMU	

Tempatron: Eltime House, Hall Road, Maldon, Essex, CM9 4NF UK.



Tempatron Industrial Controls is a division of Eltime Ltd.

© Eltime Ltd. Tempatron TFDRMU Timer 06/2020

Specification

Accuracy:

- Repeat accuracy: ±3sec/24hours

Power Supply Voltage:

- 24 to 240Vac/dc

Burden

<3VA

Frequency:

- 50/60Hz

Time Ranges:

- 0 to 9999sec
- 0 to 9999min

Relay Outputs:

- Single pole changeover contact and single pole N/O contact

Contact Ratings:

- 8A at 240Vac/30Vdc (resistive)

Electrical Contact Life:

- 100,000 operations at rated output

Reset Time:

100ms approx.

Operating Temperature:

- -5°C to 45°C

Storage Temperature:

- -10°C to 55°C

Display:

- Backlit LCD display

Enclosure Code:

- Case IP20

Weight:

- 140g

Markings:

- CE marked (meets low voltage and EMC directives)

Specification subject to change without notice.