

SITOP MODULAR/3AC/24VDC/20A

SITOP modular 20 A stabilized power supply input: 400-500 V 3 AC output: 24 V DC/20 A *Ex approval no longer available*



Input	
type of the power supply network	3-phase AC
supply voltage at AC	
<ul style="list-style-type: none"> • minimum rated value • maximum rated value • initial value • full-scale value 	400 V 500 V 320 V; Starting from $V_{in} > 340$ V 550 V
design of input wide range input	Yes
overvoltage overload capability	$2.3 \times V_{in}$ rated, 1.3 ms
operating condition of the mains buffering	at $V_{in} = 400$ V
buffering time for rated value of the output current in the event of power failure minimum	6 ms
operating condition of the mains buffering	at $V_{in} = 400$ V
line frequency	
<ul style="list-style-type: none"> • 1 rated value • 2 rated value 	50 Hz 60 Hz
line frequency	47 ... 63 Hz
input current	
<ul style="list-style-type: none"> • at rated input voltage 400 V • at rated input voltage 500 V 	1.1 A 0.9 A
current limitation of inrush current at 25 °C maximum	35 A
I ² t value maximum	0.7 A ² ·s
fuse protection type	none
<ul style="list-style-type: none"> • in the feeder 	Required: 3-pole connected miniature circuit breaker 6 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
<ul style="list-style-type: none"> • at output 1 at DC rated value 	24 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
<ul style="list-style-type: none"> • on slow fluctuation of input voltage • on slow fluctuation of ohm loading 	0.1 % 0.2 %
residual ripple	
<ul style="list-style-type: none"> • maximum 	100 mV
voltage peak	
<ul style="list-style-type: none"> • maximum 	200 mV
adjustable output voltage	24 ... 28.8 V

product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer; max. 480 W
display version for normal operation	Green LED for 24 V OK
type of signal at output	via signaling module (6EP1961-3BA10)
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	2.5 s
voltage increase time of the output voltage <ul style="list-style-type: none"> • maximum 	500 ms
output current <ul style="list-style-type: none"> • rated value • rated range 	20 A 0 ... 20 A; +60 ... +70 °C: Derating 2%/K
supplied active power typical	480 W
short-term overload current <ul style="list-style-type: none"> • at short-circuit during operation typical 	60 A
duration of overloading capability for excess current <ul style="list-style-type: none"> • at short-circuit during operation 	25 ms
constant overload current <ul style="list-style-type: none"> • on short-circuiting during the start-up typical 	23 A
product feature <ul style="list-style-type: none"> • bridging of equipment 	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
Efficiency	
efficiency in percent	90 %
power loss [W] <ul style="list-style-type: none"> • at rated output voltage for rated value of the output current typical 	53 W
Closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	2 %
setting time <ul style="list-style-type: none"> • load step 50 to 100% typical • load step 100 to 50% typical 	4 ms 4 ms
setting time <ul style="list-style-type: none"> • maximum 	10 ms
Protection and monitoring	
design of the overvoltage protection	< 35 V
response value current limitation typical	23 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Alternatively, constant current characteristic approx. 23 A or latching shutdown
enduring short circuit current RMS value <ul style="list-style-type: none"> • typical 	23 A
display version for overload and short circuit	LED yellow for "overload", LED red for "latching shutdown"
Safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra-low output voltage Uout acc. to EN 60950-1 and EN 50178
operating resource protection class	Class I
leakage current <ul style="list-style-type: none"> • maximum 	3.5 mA
protection class IP	IP20
Approvals	
certificate of suitability <ul style="list-style-type: none"> • CE marking • UL approval • CSA approval • cCSAus, Class 1, Division 2 	Yes Yes; UL-Listed (UL 508), File E197259; CSA (CSA C22.2 No. 14, CSA C22.2 No. 107.1) Yes; UL-Listed (UL 508), File E197259, CSA (CSA C22.2 No. 14, CSA C22.2 No. 107.1) No

<ul style="list-style-type: none"> • ATEX 	No
certificate of suitability	
<ul style="list-style-type: none"> • IECEx • NEC Class 2 • ULhazloc approval • FM registration 	No No No No
type of certification CB-certificate	No
certificate of suitability	
<ul style="list-style-type: none"> • EAC approval 	Yes
certificate of suitability shipbuilding approval	Yes
shipbuilding approval	ABS, GL
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) 	Yes No Yes No No
EMC	
standard	
<ul style="list-style-type: none"> • for emitted interference • for mains harmonics limitation • for interference immunity 	EN 55022 Class B EN 61000-3-2 EN 61000-6-2
environmental conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during transport • during storage 	0 ... 70 °C; with natural convection -40 ... +85 °C -40 ... +85 °C
environmental category acc. to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
Mechanics	
type of electrical connection	screw-type terminals
<ul style="list-style-type: none"> • at input • at output • for auxiliary contacts 	L1, L2, L3, PE: 1 screw terminal each for 0.2 ... 4 mm ² single-core/finely stranded +, -: 2 screw terminals each for 0.33 ... 4 mm ² -
width of the enclosure	160 mm
height of the enclosure	125 mm
depth of the enclosure	125 mm
required spacing	
<ul style="list-style-type: none"> • top • bottom • left • right 	50 mm 50 mm 0 mm 0 mm
net weight	2 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
electrical accessories	Buffer module, signaling module
MTBF at 40 °C	711 213 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

