



- Speeds routing of wires
- Uniform driving depth is insured by a collar stop
- Smooth finish on nails prevents abrasion on wire jackets

Part Number: HBN2.5-T
Product Family: Harness Board Nails
Product Line: Harness Board Accessories

RoHS Compliancy Status: RoHS directive is not applicable

Part Description: Harness Board Nail

Material: Nickel Plated Steel

Diameter (In.): .107

Diameter (mm): 2.7

Length (In.): 2.50

Length (mm): 63.5

Environment: Indoors

Mounting Method: Hammered into Harness Board

Overall Length (In.): 3.12

Overall Length (mm): 79.2

Std. Pkg. UOM: PK

Thickness (In.): .110

Thickness (mm): 2.8

UOM: PC

Std. Pkg. Qty.: 200

Min. Order Qty.: 200