

58573-1 ✓ ACTIVE

AMP

TE Internal #: 58573-1

Portable Crimp Tools, Commercial Crimp Tooling, Removable /Interchangeable, UL/CSA / TE Product Specification (114-), Battery / Manual / Electric

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-), UL/CSA**

TE Certification: **Upon Request for Fee**

Power Technology Type: **Battery, Electric, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-), UL/CSA
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	PRO-CRIMPER Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content












Solder Process Capability

Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 324486 SPARE WIRE CAP,BLU .120-.145 INS.</p>	 <p>TE Part # 324487 SPARE WIRE CAP,YEL .150-.210 INS.</p>	 <p>TE Part # 324484 SPARE WIRE CAP,NAT .048-.075 INS.</p>	 <p>TE Part # 2-324485-1 WIRE CAP RED .080-.115</p>
 <p>TE Part # 324693 SPARE WIRE CAP,NAT, .048-.075 INS., MOIS</p>	 <p>TE Part # 324694 SPARE WIRE CAP,RED .080-.115 INS., MOIS.</p>	 <p>TE Part # 324695 SPARE WIRE CAP,BLU .120-.145 INS., MOIS.</p>	 <p>TE Part # 324696 SPARE WIRE CAP,YEL .150-.210 INS., MOIS</p>
 <p>TE Part # 324485 SPARE WIRE CAP,RED .080-.115 INS.</p>	<p>TE Part # 8-324485-0 WIRE CAP,RED .080 - .115</p>		

Customers Also Bought



Documents

Datasheets & Catalog Pages

[1-1773865-2_1015_Commercial Manual Hand Tools](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

[Bottoming Dies](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English