5" Sealed Back Midrange



: Re: 7Ω

: Fs: 446Hz

: D: 98mm

: Xmax: 1.35mm

: Le(1K): 0.61mH



Specifications

Dimensions : 5" (131.5mm)

Impedance : 80

Input: Rated 25W, Max. 50W

Free Air Resonance : 500 ±100Hz

Sensitivity : 91±2 δB/W/M, 2.83V

Frequency Range : FO ~ 10000Hz

Sine Wave Test : 8V

Weight : 950 grams

Life Test : 50W, 8H, EIA white noise

Parameters

DC Resistance

Resonance Frequency

Driver Piston Diameter

Voice Coil Inductance

Linear Displacement

Basket : Stamped Steel
Dust Cap : Coated Paper

Voice Coil

Diameter : 25.4mm
Length : 6.7mm
Layer : 2mm

Former Material : Aluminium (ASV) Wire Material : Copper (SVW)

Cone Paper

Cone Material : Coated Paper

Surround Material : Foam

Magnet


 Diameter
 : 100mm

 Height
 : 15mm

 Material
 : Ferrite

 Weight
 : 377g

 Gap(H)
 : 4mm





Part Number Table

Description	Part Number
5" Sealed Back Midrange	54-360

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

