
2390144-3 - ACTIVE

HPI

TE Internal #: 2390144-3 HPI, Housing, Receptacle, Wire-to-Board, 3 Position, 1.25 mm [.049 in] Centerline, Crimp, 1 Row, Natural, Mating Retention, Wire & Cable

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: Housing Connector & Housing Type: Receptacle Connector System: Wire-to-Board Number of Positions: 3 Centerline (Pitch): 1.25 mm [.049 in]

Features



Product Type Features

| Connector Product Type | Housing |
|---------------------------------------|---------------|
| Connector & Housing Type | Receptacle |
| Connector System | Wire-to-Board |
| Sealable | No |
| Connector & Contact Terminates To | Wire & Cable |
| Configuration Features | |
| Number of Positions | 3 |
| Number of Rows | 1 |
| Electrical Characteristics | |
| Termination Resistance | 20 mΩ |
| Dielectric Withstanding Voltage (Max) | 500 VAC |
| Insulation Resistance | 100 MΩ |
| Operating Voltage | 50 V |
| Contact Features | |

HPI, Housing, Receptacle, Wire-to-Board, 3 Position, 1.25 mm [.049 in] Centerline, Crimp, 1 Row, Natural, Mating Retention, Wire & Cable



| Contact Current Rating (Max) | 1 A |
|--|----------------------------|
| Termination Features | |
| Termination Method to Wire & Cable | Crimp |
| Mechanical Attachment | |
| Strain Relief | Without |
| Panel Mount Feature | Without |
| PCB Mount Retention | Without |
| Mating Retention | With |
| Connector Mounting Type | Cable Mount (Free-Hanging) |
| Housing Features | |
| Housing Entry Configuration | Both Ends Closed |
| Housing Material | 66 Nylon |
| Centerline (Pitch) | 1.25 mm[.049 in] |
| Housing Color | Natural |
| Dimensions | |
| Accepts Wire Insulation Diameter Range | .7 – 1.1 mm |
| Wire Size | .05 – .2 mm² |

Usage Conditions

| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F] |
|---|-------------------------------|
| Operation/Application | |
| Circuit Application | Power & Signal |
| Industry Standards | |
| Glow Wire Rating | Standard Part - Not Glow Wire |
| UL Flammability Rating | UL 94V-0 |
| Packaging Features | |
| Packaging Quantity | 1000 |
| Packaging Method | Bag & Box |
| Product Compliance | |
| For compliance documentation, visit the product page on TE.com> | |
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| | |

C For support call+1 800 522 6752

HPI, Housing, Receptacle, Wire-to-Board, 3 Position, 1.25 mm [.049 in] Centerline, Crimp, 1 Row, Natural, Mating Retention, Wire & Cable



| EU ELV Directive 2000/53/EC | Not Yet Reviewed |
|---|---|
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-

Compatible Parts




HPI, Housing, Receptacle, Wire-to-Board, 3 Position, 1.25 mm [.049 in] Centerline, Crimp, 1 Row, Natural, Mating Retention, Wire & Cable





Also in the Series | HPI



Customers Also Bought



TE Part #1855118-1
TE Part #2-1241817-3

U POD .187 STRAIGHT SAPR090F140F
STD TIM HOUSING MKII 3POS

LM & G
Image: Compare the second second

TE Part #63496-1TE Part #530.POWER RING TERMINAL TAB 16-10RNF-150-1/4AWG BRRNF-150-1/4





TE Part #440452-000

RT-3-NO.1-0-2.25IN

HPI, Housing, Receptacle, Wire-to-Board, 3 Position, 1.25 mm [.049 in] Centerline, Crimp, 1 Row, Natural, Mating Retention, Wire & Cable



Documents

Product Drawings 1.25P 3POS WTB CABLE HSG NA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2390144-3_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2390144-3_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2390144-3_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications Product Specification

English