

M12 Connector

TE Internal #: T4130012031-000

M12 Connector, Standard Circular Connectors, Wire-to-Panel, 3

Position, Sealable, Wire & Cable, 4A Contact Current Rating (Max),

Signal

View on TE.com >



Connectors > Circular Connectors > Standard Circular Connectors > M12 Panel Mount Solder Cups











Connector System: Wire-to-Panel

Number of Positions: 3

Sealable: Yes

Connector & Contact Terminates To: Wire & Cable

Contact Current Rating (Max): 4A

All M12 Panel Mount Solder Cups (56)

Features

Product Type Features

Product Type	Connector
Accessory Color	Black
Assembly Type	Electrical Connector
Connector System	Wire-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Keying & Polarized Position Locations	A
Factory Installed Backshell	No
Keying	A
Number of Positions	3



Number of Power Positions	0
Number of Signal Positions	3
Contacts Preloaded	Yes
Electrical Characteristics	
Operating Voltage	250 VAC
Body Features	
Peripheral Seal Material	Silicone
Environmental Protection	IP67
O-Ring Material	Silicone
Environmental Protection Type	Elastomer Sealed
Shell Plating Material	Nickel
Shell Base Material	Copper Alloy
Circular Connector Insulation Material Type	Polyamide 66 GF25
Contact Features	
Contact Current Rating (Max)	4 A
Reverse Gender	Yes
Circular Connector Contact Type	Pin
Mechanical Attachment	
Polarization Code	A
Housing Features	
Circular Connector Shell Size	18
Dimensions	
Wire Size	18 – 24 AWG
Usage Conditions	
IP Water Sealing Level	IP67
Operating Temperature Range	-40 - 85 °C[-40 - 185 °F]
Operation/Application	
Circuit Application	Signal
Shielded	No
Industry Standards	
UL Flammability Rating	НВ



Packaging Features

Packaging Quantity	1
Other	
Field Serviceable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





TE Part # 1991134-2 M12 Mtl Female B-Code Pnl, PCB Front, Hx

Also in the Series | M12 Connector







Circular Connector Adapters(2)

Standard Circular Connectors(453)

Customers Also Bought



M12 Field Installable Unshielded









Documents

Product Drawings

M12,REAR MOUNT,MALE,A,3P,SOLDER WIRE

English

CAD Files

3D PDF

3D



Customer View Model

ENG_CVM_CVM_T4130012031-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T4130012031-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T4130012031-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

M8 / M12 Connector System Catalog

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

UL Report

English