

Hand Protection



SEAMLESS LATEX COATED GLOVES

DURO TASK

Rough, blue, natural rubber coating in combination with a seamless cotton/polyester liner provide excellent grip, high comfort and also finger sensitivity. Used for various kinds of general purpose applications like assembly work, construction industry, warehousing, etc.



| art.no. | sizes |
|-------------|----------------------------------|
| NF14 | 7S, 8M, 9L, 10XL, 11XXL |
| Standards | EN420, EN388 (3142) |
| CE Category | Intermediate Design |
| Packaging | 12 pairs/polybag, 144 pairs/case |

DURO TASK PLUS

Natural rubber coating in combination with 100% Kevlar seamless liner providing excellent cut protection and grip. Glass industry and other high cut risk areas are the main applications.



| art.no. | sizes |
|-------------|-------------------------------|
| NFK14 | 7S, 8M, 9L, 10XL |
| Standards | EN420, EN388 (3443) |
| CE Category | Intermediate Design |
| Packaging | 12 pairs/pack, 144 pairs/case |

DURO TASK SUB ZERO

Seamless special brushed synthetic liner for good insulation as well as good comfort, fit and especially good finger dexterity compared to other winter gloves. Palm coating made of rough latex for good grip also in wet applications. A good all-round glove for various general purpose applications in cold environments



| art.no. | sizes |
|-----------|--|
| NF14HD | 8M, 9L, 10XL, 11XXL |
| Standards | EN420, EN388, EN511 CE Category: intermediate design |
| Packaging | 12 pairs per polybag, 144 pairs per case |

SEAMLESS PU COATED GLOVES

LIGHT TASK

Seamless nylon liner to provide excellent fit and comfort, coated with Polyurethane to give good grip and dexterity. The good fit and grip allows the worker a high work efficiency.



| art.no. | description | sizes | EN388 |
|-----------|--|-------------------------|-------|
| NF15 | nylon liner, white | 7S, 8M, 9L, 10XL, 11XXL | 4131 |
| NF15B | nylon liner, black | 7S, 8M, 9L, 10XL, 11XXL | 4131 |
| Standards | EN420, EN388 CE category Intermediate Design | | |
| Packaging | 12 bags per polybag, 144 pairs per case | | |

LIGHT TASK PLUS

Seamless grey and white Dyneema liner to combine high cut resistance, fit comfort and dexterity. Cut level 3 according to CE norm. Coated with white Polyurethane. The good fit and grip allows the worker a high work efficiency. Used in all general purpose applications, where cut resistance and finger dexterity is important



| art.no. | sizes | EN388 |
|-----------|--|-------|
| NFD16 | 7S, 8M, 9L, 10XL, 11XXL | 4343 |
| Standards | EN420, EN388 CE category intermediate design | |
| Packaging | 12 pairs per polybag, 144 pairs per case | |

LIGHT TASK PLUS 5

Seamless dyneema glass fibre liner for highest cut protection according to level 5 as per EN388. Blue/white liner coated with grey polyurethane to give good grip and dexterity. Furthermore this glove is treated with a special "anti-wet" coating to make it moisture repellent. The ideal combination for high finger sensitivity and still very high cut protection



| art.no. | sizes |
|-----------|--|
| NFD20 | 7S, 8M, 9L, 10XL, 11XXL |
| Standards | EN420, 2003, EN388, 2003 CE category intermediate design |
| Packaging | 12 pairs per polybag, 48 pairs per case |

BUTYL GLOVES

BUTYL

Butyl unsupported gauntlet, specially designed for handling Ketones (MEK, MIBK, Acetone) and Esters (Tricresyl Phosphate, Amyl Acetate, Ethyl Acetate). Butyl exhibits the highest permeation resistance to gas or



water vapour. B131R, B174R+ B324R with Grip safe palm.



| art.no. | description | sizes | Thickness |
|-----------|---|-------------------------|-----------|
| B131 | 28 cm, smooth finish | 7S, 8M, 9L, 10XL, 11XXL | 0.33 mm |
| B131R | 28 cm, rough finish | 7S, 8M, 9L, 10XL, 11XXL | 0.33 mm |
| B174 | 35cm, smooth finish | 8M, 9L, 10XL, 11XXL | 0.43 mm |
| B174R | 35cm, rough finish | 8M, 9L, 10XL, 11XXL | 0.43 mm |
| B324 | 35cm, smooth finish | 8M, 9L, 10XL, 11XXL | 0.81 mm |
| B324 R | 35cm, rough finish | 8M, 9L, 10XL, 11XXL | 0.81 mm |
| Materials | Black unsupported Butyl gauntlet. | | |
| Standards | EN420, EN388 (4111), EN374. CE Category Complex Design | | |
| Packaging | 1 pair per bag, 24 pairs per case B131 + B131R + B174 + B174R | | |
| Packaging | 1 pair per bag, 12 pairs per case B324 + B324R | | |