
# //LPS//LPINE

Rotary Potentiometer > RK09K/RK09D Series > RK09K1130AH1

9mm Size Insulated Shaft Snap-in Type RK09K/RK09D Series

#### Dimensions | Mounting Hole Dimensions | Terminal Layout / Circuit Diagram | Packing Specifications | Soldering Conditions |






| Number of resistor elements                 |                               | Single-unit<br>(20V DC) |
|---------------------------------------------|-------------------------------|-------------------------|
| Control part orientation (Installed height) |                               | Vertical type           |
| Collar (Sleeve type)                        |                               | Without                 |
| Shaft types                                 |                               | Flat                    |
| Length of the shaft LM1                     |                               | 25mm                    |
| Center detent                               |                               | Without                 |
| Total resistance                            |                               | 10k Ω                   |
| Resistance taper                            |                               | 1B                      |
| Operating temperature                       | range                         | -10°C to +70°C          |
| Electrical Performance                      | Total resistance<br>tolerance | ±20%                    |
|                                             | Rated power                   | 0.05W                   |
|                                             | Maximum operating<br>voltage  | 50V AC, 20V DC          |
|                                             | Insulation resistance         | 100MΩ min. 250V DC      |
|                                             | Voltage proof                 | 250V AC for 1 minute    |
| Mechanical<br>Performance                   | Total rotational angle        | 280° ±5°                |
|                                             | Rotational torque             | 1 to 8mN·m              |


#### RK09K/RK09D Series - Basic information

|                              | Stopper strength   | 0.3N·m                                                                                                                               |
|------------------------------|--------------------|--------------------------------------------------------------------------------------------------------------------------------------|
|                              | Push-pull strength | 50N max.                                                                                                                             |
|                              | Vibration          | 10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z and for 2 hours respectively |
| Durability                   | Operating life     | 5,000 cycles                                                                                                                         |
| Minimum order unit<br>(pcs.) | Japan              | 1,000                                                                                                                                |
| 7F                           | Export             | 2,000                                                                                                                                |


## Dimensions



Mounting Hole Dimensions



# Terminal Layout / Circuit Diagram



### **Packing Specifications**

| Number of packages<br>(pcs.)     | 1 case / Japan             | 1,000           |
|----------------------------------|----------------------------|-----------------|
|                                  | 1 case / export<br>packing | 2,000           |
| Export package measurements (mm) |                            | 528 × 369 × 178 |

#### **Soldering Conditions**

| Tip temperature | 350°C max. |
|-----------------|------------|
| Soldering time  | 3s max.    |
| No. of solders  | 1 time     |

#### Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
  Please place purchase orders per minimum order unit (integer).
  Products other than those listed in above products are also available. Please contact us for details.

## Inquiries about Products

Inquiry