Analog Audio CAT5 Extender

pro-signal



RoHS Compliant

Features

- Used in pairs via CAT5 UTP cable to send audio signal up to 600 meters.
- RCA female to 2 pin screw terminal.
- · 20Hz to 20kHz Bandwidth.
- Available for 75Ω to 20Ω cable.
- · Hi Performance to eliminate the audio ground loop interference.

Specifications

Audio Input / Output	RCA × 1
Audio Input	2V p-p, 75Ω
Link Connector	Terminal × 1
Link Cable	Twisted Pair CAT5 (AWG24)
Dimensions	59.3mm × 25mm × 20.7mm
Weight	25g

Part Number Table

Description	Part Number
Analog Audio CAT5 Extender	PSG08198

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

