MODEL MM7100-2D ThermoBarScan

Waterproof ThermoBarScan Thermometer with 1D/2D Scanner & Large Display

FEATURES

A handheld logging thermometer with integral barcode scanner for recording product location/identity plus time, date and temperature. This thermometer features a large display for more barcode information, scrolling buttons and Bluetooth communication for data transmittal to PC

*** °C / °F switchable

*** Resolution of 0.1° to 1000° autoranging

*** Switchable thermocouple types K / T / J / R / N / E / S

*** Infra-Red sensor compatability

*** Full retention of thermocouple type and temperature scale

*** User configurable Auto Switch Off capability

** Overrange / Open circuit sensor indication

*** Low battery indication

*** IP65 casing complete with protective rubber boot

*** Integral Barcode reader for 1D and 2D barcode formats

*** Free downloadable software

SPECIFICATION

Environmental

AMBIENT OPERATING RANGE : 0 to 50 $^{\circ}$ C STORAGE TEMPERATURE RANGE : -20 to 50 $^{\circ}$ C HUMIDITY : 0 to 70% R.H.

ELECTRICAL

MEASUREMENT RANGES : K -200 to 1372 °C
T -200 to 400 °C
J -200 to 1200 °C
R 0 to 1767 °C
N -200 to 1200 °C

E -200 to 1000 °C S 0 to 1767 °C

THERMOCOUPLE TYPES : K T J R N E S INFRA-RED SENSOR (Exergen K80) : K80 –50 to 250 $^{\circ}$ C

TEMPERATURE SCALES : $^{\circ}$ C / $^{\circ}$ F

ACCURACY @23°C : +/- 0.1% OF READING +/- 0.2 °C

CHARACTERISING ACCURACY : LESS THAN 0.05 $^{\circ}$ C TEMPERATURE COEFFICIENT : 0.01% OF READING / $^{\circ}$ C

COLD JUNCTION COMPENSATION : 0.0075 °C/°C RESOLUTION : 0.1° to 1000, 1° ABOVE 1000

BARCODE

READABLE BARCODES : All UPC/EAN/JAN Codes

EAN28 Codes Code39 Code128

PDF417 QR Code Data Matrix GS1-DataBarTM

RSS, RSS Limited, RSS-14 RSS-14 Stacked, RSS-Expand **BLUETOOTH**

CLASS : Class I

CONTAINS : fcc ld: S22btmodule-Cl1

GENERAL

BATTERY : PP3 9V I.E.C. 6F22

BATTERY LIFE (INTERMITTENT USE) : GREATER THAN 200 HOURS (ALKALINE)

WEIGHT : 200 gms

DIMENSIONS : 160 X 50 X 30 mm

Cross-reference for compatible probes

Suitable probes and accessories for use with this instrument

TME PART No	DESCRIPTION	APPLICATION	T/C TYPE
KP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
TP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
KP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
TP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
TP10	SOUS VIDE NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
KM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	Т
VCO1	SLIDEACE BAND DDODE	FAST RESPONSE SURFACE MEASUREMENT	V
KS01 TS01-S	SURFACE BAND PROBE DUAL PROBE	FOR SURFACE AND IMMERSION MEASUREMENT	K
	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	K
TS04	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT GENERAL PURPOSE SURFACE MEASUREMENT	T
	HIGH TEMP SURFACE PROBE	HIGH TEMPERATURE SURFACE MEASUREMENT	K
KS08	HIGH TEMP SURFACE PROBE	HIGH TEMPERATURE SURFACE MEASUREMENT	K
KA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	К
TA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	Т
TA12	SPATULA PROBE	BETWEEN PACK PROBE	Т
KH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	K
TH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	T
KHA02	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	K
THA2	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	T
KHM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
THM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KHN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
THN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
THA12	PLUG MOUNTED SPATULA PROBE	BETWEEN PACK PROBE	Ť
KHS01	PLUG MOUNTED SURFACE BAND PROBE	FAST RESPONSE SURFACE MEASUREMENT	K
KHS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	K
THS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	Т
BIG II G	10/46/47	DDODE WIT DESIGNED FOR THE UNIVERSITY	
PKHV1	HVAC KIT	PROBE KIT DESIGNED FOR THE HVAC INDUTRY	K
PKF1	FOOD KIT	PROBE KIT DESIGNED FOR THE FOOD INDUTRY	T
PKGP1	GENERAL PURPOSE KIT	PROBE KIT CONTAINING MOST POPULAR PROBES	K
TP01	CORKSCREW PROBE	PROBE DESIGNED FOR CORE TEMPERATURE OF MEAT	Т
1101	CONNECTED TROBE	TROBE DESIGNED FOR CORE TENTERATORE OF MEAT	
KPS10	PIPE CLAMP PROBE	PROBE DESIGNED TO BE CLAMPED ONTO PIPES	K
TFS01	FOOD SIMULANT PROBE	SIMULATES THE CORE TEMPERATURE OF FOOD IN HOT OR COLD STORAGE	