

3W, AC-DC converter

RoHS Compliant

Features

- Ultra-wide 85 305V AC and 100 430VDC input voltage range
- 1" × 1" compact size
- Operating ambient temperature range: -40°C to +85°C
- Up to 81.5% efficiency
- · No-load power consumption 0.1W
- · 5000m altitude application
- Plastic case meets UL94V-0 flammability
- EMI performance meets CISPR32 / EN55032 CLASS B, EN55014



Description

MP-LD03-23BxxR2 series AC-DC converters is one of compact size power converter. It features ultra-wide AC input and at the same time accepts DC input voltage, low power consumption, high efficiency, high reliability, reinforced isolation. It offers good EMC performance compliant to IEC/EN61000-4 and CISPR32/EN55032 and meets IEC/EN/UL62368/EN60335/EN61558 standards. The converters are widely used in industrial, power, home appliances, instrumentation, communication and civil applications. For extremely harsh EMC environment, we recommend using the application circuit show in Design Reference of this datasheet.

Selection Guide					
Part Number	Output Power	Nominal Output Voltage and Current	Efficiency at 230VAC (%) Typ.	Capacitive Load (µF) Max.	
MP-LD03-23B03R2		3.3V/900mA	72	4000	
MP-LD03-23B05R2		5V/600mA	76	3000	
MP-LD03-23B09R2	3W	9V/333mA	70	4000	
MP-LD03-23B12R2		12V/250mA	78	1200	
MP-LD03-23B24R2		24V/125mA	79	220	

Input Specifications					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
Innut Valtage Bange	AC input	85		305	V AC
Input Voltage Range	DC input	100]	430	V DC
Input Frequency		47	-	63	Hz
Innut Current	115V AC]	0.08	
Input Current	230V AC			0.06] ,
Januara Cumant	115V AC		15	-	A
Inrush Current	230V AC		25	-]
Leakage Current	277V AC/50Hz		0.25mA F	RMS Max.	
Recommended External Input Fuse			1A, slow-bloe actual use no ding to the app		
Hot Plug			Unava	ailable	





Output Specifications		'				
Item	Operating Conditions	Min.	Тур.	Max.	Unit	
Outrout Valtage Aggregati	3.3V output		±3	-		
Output Voltage Accuracy	others		±2	-	%	
Linear Regulation	Full load		±0.5	-	%	
Load Regulation	0%-100% load		±1	-		
Ripple & Noise*	20MHz bandwidth (peak-to-peak value)		50	100	mV	
Stand-by Power Consumption	230V AC		0.10	-	W	
Temperature Coefficient			±0.02	-	%/°C	
Short-circuit Protection		Hiccu	Hiccup, continuous, self-recover		elf-recovery	
Over-current Protection		2	≥200%lo, self-recovery		covery	
	3.3/5V DC output		≤7.5V DC			
O	9V DC output		≤15V DC			
Over-voltage Protection	12V DC output		≤16V DC			
	24V DC output		≤30V DC			
Minimum Load		0	-	-	%	
Hald up Tipes	115V AC input	-	5	-		
Hold-up Time	230V AC input	-	50	-	ms	

Notes: *The "Tip and barrel method" is used for ripple and noise test, output parallel 10uF electrolytic capacitor and 1uF ceramic capacitor, please refer to AC-DC Converter Application Notes for specific information.

General Specifications

	Item	Operating Conditions		Min.	Тур.	Max.	Unit
Isolation	Input-Output	Electric Strength Test for 1min, leakage current <5mA			-	-	V AC
Operating	Temperature			40	-	+85	°C
Storage T				-40	-	+105	
Storage F	Humidity			-	-	+95	%RH
Coldorina	Tomporatura	Wave-soldering			260 ± 5°C;	time: 5 - 10)s
Soldering	Temperature	Manual-welding			360 ± 10°C	C; time: 3 - 5	- S
Switching	Frequency			-	65	-	kHz
		+70°C to +85°C	3.3V	2.33	-	-	%/°C
Power De	erating		Others	1.33	-	-	
		85V AC - 100V AC		1.33	-	-	%/VAC
Altitude				-	-	5000	m
Safety St	andard				62368-1, EN Approval &		
Safety Cla	ass				CL/	ASS II	
MTBF				MIL-HDBK-217F@25°C > 2799,000 h			99,000 h
Dooignod	Danisma d Life	2201/ A.C	Ta:25°C 100% load	>150 × 10 ³ h			
Designed Life	230V AC Ta: 55°C 100% load		>27 × 10 ³ h				





Mechanical Specifications				
Case Material		Black plastic; flame-retardant and heat-resistant (UL94 V-0)		
Dimensions	Horizontal package	25.4mm × 25.4mm × 17.6mm		
Weight Horizontal package		18g (Typ.)		
Cooling Method		Free air convection		

Electron	nagnetic Compati	bility (EMC)				
		CISPR32/EN55032	CLASS B			
	CE	CISPR32/EN55032 CLASS B (See Fig.3 for recommended circuit)				
		EN55014-1				
Emissions		CISPR32/EN55032	CLASS B			
	DE	CISPR32/EN55032	CLASS B (see Fig. 5-2 for recommended circ	uit)		
	RE	EN55014-1				
	500	IEC/EN61000-4-2	Contact ±6KV/Air ±8KV	perf. Criteria B		
	ESD	EN55014-2		perf. Criteria B		
	RS	IEC/EN61000-4-3	10V/m	perf. Criteria A		
	l KS	EN55014-2		perf. Criteria A		
		IEC/EN61000-4-4	±2KV (See Fig.1 for typical application circuit)	perf. Criteria B		
	EFT	IEC/EN61000-4-4	±4KV (See Fig.2 for recommended circuit)	perf. Criteria B		
		IEC/EN61000-4-4	±4KV (See Fig.3 for recommended circuit)	perf. Criteria A		
		EN55014-2		perf. Criteria B		
		IEC/EN61000-4-5	line to line ±1KV	norf Critoria B		
Immunity	Curre		(See Fig.1 for typical application circuit)	perf. Criteria B		
,,	Surge	IEC/EN61000-4-5	line to line ±2KV	nami Cuitania D		
			(See Fig.2 for recommended circuit)	perf. Criteria B		
		IEC/EN61000-4-5	line to line ±2KV/line to ground ±4KV	norf Critoria A		
			(See Fig.3 for recommended circuit)	perf. Criteria A		
		EN55014-2		perf. Criteria B		
	cs	IEC/EN61000-4-6	10Vr.m.s	perf. Criteria A		
		EN55014-2		perf. Criteria A		
	Voltage dip, short	IEC/EN61000-4-11	0%, 70%	perf. Criteria B		
	interruption and voltage variation	EN55014-2		perf. Criteria B		


Note: When the output terminal of the product needs to be connected to PE through a Y capacitor, or close to the metal frame, please refer to the Fig.3 for recommended circuit.






multicomp PRO


Typical Characteristic Curves






Note: ① With an AC input between 85-100V/ a DC input between 100-120VDC, the output power must be derated as per temperature derating curves;

② This product is suitable for applications using natural air cooling; for applications in closed environment please consult factory or one of our FAE.





Design Reference

1. Typical application




Fig. 1: Typical circuit diagram

Part Number	C1(µF)	C2(µF)	FUSE	R1	TVS	MOV	
MP-LD03-23B03R2		150			SMBJ7A		
MP-LD03-23B05R2		150	1A/300V,	12Ω/3W	SIVIDJ/A		
MP-LD03-23B09R2	1	120	slow-blo	slow-blow,	(wire-wound resistor.	SMBJ12A	S10K350
MP-LD03-23B12R2				120	required	required)	SMBJ20A
MP-LD03-23B24R2		68		·	SMBJ30A		

Output Filter Components:

We recommend using an electrolytic capacitor with high frequency, and low ESR rating for C2 (refer to manufacture's datasheet). Choose a Capacitor voltage rating with at least 20% margin, in other words not exceeding 80%. C1 is a ceramic capacitor used for filtering high-frequency noise and TVS is a recommended suppressor diode to protect the application in case of a converter failure.





2. EMC compliance recommended circuit




Fig. 2: EMC application circuit with higher requirements

Component	Recommended value
MOV	S14K350
R1	33Ω/3W (wire-wound resistor, required)
FUSE	2A/300V, slow-blow, required






Fig. 3: Recommended circuit for class I equipment


Component	Recommended value		
FUSE	2A/300V, slow-blow, required		
MOV	S14K350		
CX	334K/305VAC		
R1	33Ω/3W (wire-wound resistor, required)		
L1	1.2mH/0.3A		
CY1/CY2	1nF/400VAC		
GDT	300V/1KA		
LCM	20 mH, P/N: FL2D-10-203 is recommended		
Note: Rx1/Rx2/Rx3/Rx4/Rx5/Rx6 is the bleeder resistance of CX, and the recommended resistance value is 1.5MΩ/150V DC.			



Dimensions and Recommended Layout







Note: Grid 2.54*2.54mm

F	Pin-Out		
Pin	Function		
1	AC(N)		
2	AC(L)		
3	No pin		
4	-Vo		
5	+\/0		

Note:

Unit: mm[inch]

Pin diameter tolerances: ±0.10[±0.004] General tolerances: ±0.50[±0.020]

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

