

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2084820150

Status:


Active

Overview:

Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee

Description:

Wi-Fi 6E Flex Cabled 2x2 MIMO Antenna, 150.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors



Documents:	
3D Model	Application Specification 2084820100-001 (PDF)
Drawing (PDF)	Packaging Specification 2084820100-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 2084820100-000 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Antennas
Series	208482
Component Type	Flexible Antenna with Cable
Function	Signal
Mates With	734120110 Microcoaxial RF, 50 Ohm
Overview	Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Product Name	2.4/5GHz Flexible Antenna
Protocol	BLE, BT, Thread, Wi-Fi, Zigbee
Type	Wi-Fi Antenna
UPC	191130083442
Physical	
Cable Length	150.00mm
Length	55.20mm
Mounting Style	Adhesive
Net Weight	1.628/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.16mm
Width	19.20mm
Electrical	
Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5850
Band#2 F_Start (MHz)	5150
Electrical Connectivity	Cable
Peak Gain (dBi)	2.7 @ 2.4G, 4.8 @ 5G (Port 1), 3.2 @ 2.4G, 5.7 @ 5G (Port 2)
Return Loss - S11 (dB)	< -8 < -13 (Port 1), < -9 < -13 (Port 2)
Total Efficiency	62%@2.4GHz, 70%@5GHz (Port 1), 72%@2.4GHz, 66%@5GHz (Port 2)
Material Info	
Reference - Drawing Numbers	
Application Specification	2084820100-001
Packaging Specification	2084820100-001
Product Specification	2084820100-000
Sales Drawing	2084820100-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

208482 Series

This document was generated on 09/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION