



- Low profile head design prevents protrusion of cut-off tie and reduces overall bundle size
- Fully rounded edges on head and strap so no sharp edges come in contact with cable insulation jacket
- Parallel-entry design that threads like a belt (180° entry)
- "Finger grip" shaped head assures positive grip during threading of tie
- All cable tie cross sections smaller than Light-Heavy have a curved tip that is easier to pick up from flat surfaces, allows faster initial threading and speeds installation
- Weather Resistant nylon resists ultraviolet light that can cause damage to natural nylon ties

Part Number: ILT2S-C0
Product Family: *Belt-Ty™* In-Line Weather Resistant Cable Ties
Product Line: IN-LINE Cable Ties

RoHS Compliancy Status: Compliant

Part Description: Cable Tie, Parallel-entry, 8.3", Standard cross section

Product Type: Cable Ties

Material: Weather Resistant Nylon 6.6

Color: Black

CSA Certified: Yes

UL Listed (File #E56854): Yes

UL Recognized (File #E56854):	Yes
Length (In.):	8.3
Length (mm):	211
Width (In.):	.190
Width (mm):	4.8
CE Compliant:	Yes
Cross Section:	Standard
Head Height (In.):	.140
Head Height (mm):	3.6
Head Width (In.):	.316
Head Width (mm):	8.0
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	1.88
Max. Bundle Diameter (mm):	48
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	50
Min. Loop Tensile Strength (N):	222
Std. Pkg. UOM:	PK

Thickness (In.):	.052
Thickness (mm):	1.3
Tool:	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100