

## Han Megabit Modul for PCB, GND, Female




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 008 3142
Specification	Han Megabit Modul for PCB, GND, Female
HARTING eCatalogue	<a href="https://b2b.harting.com/09140083142">https://b2b.harting.com/09140083142</a>

### Identification

Category	Inserts
Specification	Han <sup>®</sup> Megabit insert 2x 4 contacts

### Version

Termination method	Fast termination
Gender	Female
Number of contacts	8
further contacts	+ shielding
Details	With additional shield connection to the hinged frame

### Technical characteristics

Rated current	10 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	100 Mbit/s
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500



Pushing Performance

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
	EN 50467

## Commercial data

Packaging size	2
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440218 Module for industrial connectors (data)