

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0366420001

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 396 Header, Vertical with Snap-In Pegs, Through Hole, 6 Circuits, No Polarizing Key at Circuit 4, Lead-Free

Documents:

- 3D Model

Packaging Specification PK-70873-0027-001 (PDF)
- 3D Model (PDF)

Symbol Footprint Data SYM-366420001-001 (PDF)
- Product Specification PS-8619-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

8619

Signal, Wire-to-Board

KK Interconnect Solutions

KK 396

800756957685

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Circuits Detail

Color - Resin

First Mate / Last Break

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

6

6

No Polarizing Key at Circuit 4

Black

No

No

No

Yes

Yes

Brass

Tin

Tin

Polyester

2.847/g

1

Vertical

9.91mm

Yes

Yes

1.60mm

Bag

3.96mm

3.96mm

5.080µm

1.270µm

Yes

Yes

Partial

No

No

See Product Specification

Through Hole


Electrical

Current - Maximum per Contact

Voltage - Maximum

4.0A

250V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

8619 Series

Mates With

90331 Industry Standard Power Supply
Housing for Crimp Terminals

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	325

Material Info

Engineering Number	A-8619-0609
--------------------	-------------

Reference - Drawing Numbers

Packaging Specification	PK-70873-0027-001
Product Specification	PS-8619-001
Sales Drawing	SDA-8619-0609-001
Symbol/Footprint Data	SYM-366420001-001

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION