



Extruded Cable Ties made of Acetal provide an excellent solution for outdoor applications requiring strength and durability.

- Excellent solution for outdoor applications requiring strength and durability
- Ideal for securing cables in vertical ladder racks and outdoor messenger strand applications
- Weather Resistant Acetal strap body and head
- Double stainless steel, Type 302, locking barbs
- High tensile strength and high impact resistance
- Excellent chemical and moisture resistance
- 250 lb. minimum loop tensile strength
- Meets Telcordia TR-TSY-000789
- May be used with Stackable Aerial Cable Spacers SACS50-T100

Part Number: DT4EH-L0
Product Family: *Dura-Ty*[™] Cable Tie
Product Line: Dura-Ty Extruded Cable Ties

RoHS Compliancy Status: Compliant

Part Description: Cable Tie, 13.5", Extra-Heavy cross section

Product Type: Cable Ties

Material: Weather Resistant Acetal

Color: Black

CSA Certified: No

UL Listed (File #E56854):	No
UL Recognized (File #E56854):	No
Length (In.):	13.5
Length (mm):	343
Width (In.):	.500
Width (mm):	12.7
CE Compliant:	Yes
Cross Section:	Extra-Heavy
Head Height (In.):	.490
Head Height (mm):	12.4
Head Width (In.):	.718
Head Width (mm):	18.2
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	3.88
Max. Bundle Diameter (mm):	98
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	250
Min. Loop Tensile Strength (N):	1112

Std. Pkg. UOM:	PK
Thickness (In.):	.059
Thickness (mm):	1.5
Tool:	GTH, GS4EH, ST3EH
UOM:	PC
Std. Pkg. Qty.:	50
Min. Order Qty.:	50