



- Designed to attach coax or telephone cable to the support strand 1/4" (6.4mm) or 5/16" (7.9mm) to form the expansion loop and keep equipment and cables clear of pole hardware
- One-piece construction with integral 1/2" (12.7mm) spacer reduces inventory costs of separate spacer and bands, and installs faster to lower the installed cost
- Releasable and reusable

Part Number: AST15-5-C100
Product Family: Aerial Support Tie – Weather Resistant Polypropylene
Product Line: Outside Plant

Product Line: POLYPROPYLENE Cable Ties

RoHS Compliancy Status: Compliant

Part Description: Aerial Support Tie, 6.9", Integral 1/2" spacer for support strand applications

Product Type: Cable Ties

Material: Weather Resistant Polypropylene

Color: Black

CSA Certified: No

UL Listed (File #E56854): No

UL Recognized (File #E56854):	No
Length (In.):	6.9
Length (mm):	175
Width (In.):	.448
Width (mm):	11.4
CE Compliant:	Yes
Head Width (In.):	1.16
Head Width (mm):	29.5
Locking Style:	Releasable
Material Flammability Rating:	UL94 HB
Max. Bundle Diameter (In.):	1.50
Max. Bundle Diameter (mm):	38
Max. Continuous Use Temperature:	239°F (115°C)
Min. Loop Tensile Strength (Lbs.):	75
Min. Loop Tensile Strength (N):	334
Std. Pkg. UOM:	PK
Thickness (In.):	.055
Thickness (mm):	1.4
Tool:	Hand Installed Only

UOM: PC

Std. Pkg. Qty.: 100

Min. Order Qty.: 100