



REVISIONS

DOC. NO. SPC-F004 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1453	A	RELEASED	JWM	1/5/04	LS	8/17/04	JC	8/24/04
2045	B	Amp Measure Changed	JN	05/12/08	JWM	05/12/08	JWM	05/12/08



Features

- Compact Size
- Trms KW Measurement
- AC/DC Current Measurement (600A)
 - 600VAC & 600VDC, Ohm / Continuity Beeper
 - One touch DCA Zero

General Specifications

- Numerical Display: 3 ³/₄ digit LCD, max. reading 3999
- Over Range Indication: LCD will show " OL"
- Low Battery Indication: **Lo** is displayed when the battery drops below operating voltage
- Power Source: One 9V Battery (006P or IEC6F22)
- Operating Temp. & Humidity: 0°C ~ 40°C [32°F ~ 122°C] Below 80 % R.H.
- Storage Temp. & Humidity: -10°C ~ 60°C [14°F ~ 140°F] Below 70 % R.H.
- Dimensions: 192mm(L) x 64mm(W) x 31mm(H)
- Weight: Approx. 240g
- Jaw Opening Diameter: Cables to 27mm Dia.
- Includes: Carrying Case, Battery, Instruction Manual and Test Leads

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	Jeff McVicker	1/5/04	DC/AC TRMS Clamp Meter			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	Luis Serbia	8/17/04	A	72-7221	22H6393.dwg	B
APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: Millimeters		SHEET: 1 OF 2
John Cole	8/24/04					

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

DC KW (Aurorance)

Range	Resolution	Accuracy	Frequency Range	Overload Protection
40.00KW	0.01KW	±(2% + 5)	50 ~ 400Hz	420KW
400.0KW	0.1KW			

AC KW (Trms) (Aurorance)

Range	Resolution	Accuracy	Frequency Range	Overload Protection
40.00KW	0.01KW	±(2% + 5)	50 ~ 400Hz	420KW
400.0KW	0.1KW			

DC Current (Aurorance)

Range	Resolution	Accuracy	Overload Protection
400A	0.1A	±(1% + 2)	900Arms
600A	1A		

AC Current (Trms) (Aurorance)

Range	Resolution	Accuracy	Frequency Range	Overload Protection
400A	0.1A	±(1% + 5)	50 ~ 400Hz	800Arms
600A	1A			

DC Voltage (Aurorance)

Range	Resolution	Accuracy	Input Impedance	Overload Protection
400V	0.1V	±(1% + 1)	1 Megohm	600Vrms
600V	1V			

AC Voltage (Trms) (Aurorance)

Range	Resolution	Accuracy	Frequency Range	Input Impedance	Overload Protection
400V	0.1V	±(1% + 5)	50 ~ 400Hz	1 Megohm	600Vrms
600V	1V				

Resistance (Aurorance)

Range	Resolution	Accuracy	Overload Protection
400Ω	100mΩ	±(1% + 3)	600Arms
4000Ω	1Ω		

Continuity Beeper

Range	Resolution	Max Open Circuit Voltage	Overload Protection
o)))	≤38Ω	3.3V	600Vrms