




With up to 5 switching positions as well as multiple terminal, circuit and slider options, Bulgin's board mounted power slide switches can be configured to suit your needs. We also offer a wide range of voltage selector types that can be either snapped into a panel or flange mounted.

- ⊞ Ratings up to 16A, 250V ac
- ⊞ PCB and solder terminals
- ⊞ Voltage Selector Models
- ⊞ Snap in and flange mounting
- ⊞ 2, 3, 4 and 5 position
- ⊞ Choice of circuits
- ⊞ Choice of actuators







Key Features


- Slide switches
- Ratings up to 16A, 250V ac
- PCB and solder terminals
- 2, 3, 4 and 5 position
- Choice of circuits
- Choice of actuators
















Approvals and specifications

-  10A 250Vac T85
 6(3)A 250Vac T85
-  UL CSA 16A 250Vac Non Inductive
 UL CSA 4A 300Vac
 UL 65°C, file no. E45221, CSA file no. LR10990
- µ contact gap
 Please specify: Standard action (SP116) or Light
 action (SP118).
 2000 series lubrication is inorganic and does not
 degrade plastics.

Terminal	Series	Position	Circuit	Slider
K 2.8 x 0.8	2	2	10 20 30 40	0 6 7 9 A B C D E G H J K L N P R S T
R 2.8 x 0.8		3	10 20 30 40	1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 31 32 33 34 35 36 37 38 39 40
T 2.8 x 0.8 Solder			10 20 30 40	4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30


Examples



Body	Options	Dimensions		
<p>C 2 positions H 2 positions</p>  <p>A 3 positions H 3 positions</p>  <p>A 4 positions H 4 positions</p>  <p>A 5 positions</p> 	<p>Colour Call sales for custom colours. A full range is available for large orders.</p> <p>Legend printing A wide range is available For all options call sales</p>	<p>C 2 positions</p>  <p>A 3 positions</p>  <p>A 4 positions</p>  <p>A 5 positions</p> 	<p>H 2 positions</p>  <p>H 3 positions</p>  <p>H 4 positions</p> 	<p>Cut-out /PCB Matrix</p>  <p>for PCB</p>  <p>for PCB</p>  <p>for PCB</p>  <p>for PCB</p>

2000 Slide Switches - Snap fit and panel mount

10A 250Vac



115/230 is preferred legend

Key Features

- 2 way 'voltage selector'
- Ratings up to 16A, 250V ac
- Snap fit and panel mount
- PCB & solder terminals
- 2 and 3 position
- Choice of circuits
- Choice of actuators

Approvals and specifications

10A 250Vac T85
6(3)A 250Vac T85

UL CSA 16A 250Vac Non Inductive
UL CSA 4A 300Vac
UL 65°C, file no. E45221, CSA file no. LR10990

μ contact gap
Please specify: Standard action (SP116) or Light action (SP118).
2000 series lubrication is inorganic and does not degrade plastics.

Terminal	Series	Position	Circuit	Slider
K 2.8 x 0.8	2	2 Switching positions	10 	0 6 C L
R 2.8 x 0.8			20 	2 7 D M
T Solder			30 	3 8 E N
X PCB 0.8 Sq. For mounting stability switches have extra "support" terminals * Nominal - Dimension varies with body type. For exact figure call sales			40 	4 9 H P
	3 Switching positions	3 Switching positions	10 	5 A K R
			20 	S T
			30 	
			40 	

Examples



T22208E ---



T22308E ---



T2230MF ---












T22205B ---



T22305B ---



T23204B ---

Body	Options	Dimensions											
<div>B</div> <div>With mounting holes</div> <div></div>	<div>Colour</div> <div>Call sales for custom colours. A full range is available for large orders. Standard body colour is black.</div>	<div>2 Pos B</div> <div></div>	<div>3 Pos B</div> <div></div>										
<div>E</div> <div>Snap fit</div> <div></div>		<div>2 Pos E</div> <div></div>	<div></div> <div><table><tr><td>Panel thickness</td><td>Dim. Y</td></tr><tr><td>0.8-1.2</td><td>29.75/29.85</td></tr><tr><td>1.63</td><td>30.15/30.25</td></tr><tr><td>2.0</td><td>30.35/30.45</td></tr><tr><td>2.5</td><td>30.55/30.65</td></tr></table></div>	Panel thickness	Dim. Y	0.8-1.2	29.75/29.85	1.63	30.15/30.25	2.0	30.35/30.45	2.5	30.55/30.65
Panel thickness		Dim. Y											
0.8-1.2	29.75/29.85												
1.63	30.15/30.25												
2.0	30.35/30.45												
2.5	30.55/30.65												
<div>F</div> <div>Snap fit (single contact ON OFF only)</div> <div></div>	<div>2 Pos F</div> <div></div>	<div></div> <div><table><tr><td>Panel thickness</td><td>Dim. Y</td></tr><tr><td>0.8-1.2</td><td>29.75/29.85</td></tr><tr><td>1.63</td><td>30.15/30.25</td></tr><tr><td>2.0</td><td>30.35/30.45</td></tr><tr><td>2.5</td><td>30.55/30.65</td></tr></table></div>	Panel thickness	Dim. Y	0.8-1.2	29.75/29.85	1.63	30.15/30.25	2.0	30.35/30.45	2.5	30.55/30.65	
Panel thickness	Dim. Y												
0.8-1.2	29.75/29.85												
1.63	30.15/30.25												
2.0	30.35/30.45												
2.5	30.55/30.65												