

This document was generated on 09/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: <u>0442820001</u>

Status: Active

Overview: Magnetic and Modular Jacks/Plugs

Description: Modular Jack, Right-Angle, Low Profile, Shielded, Surface Mount, 8/8

Documents:

Drawing (PDF)

3D Model

Product Specification PS-43743-0001-001 (PDF)

Packaging Specification PK-70873-700-001 (PDF)

3D Model (PDF) RoHS Certificate of Compliance (PDF)

Agency Certification

CSA LR19980 UL E107635

General

Product Family Modular Jacks/Plugs

Series <u>44282</u>
Component Type PCB Jack
Magnetic No

Overview <u>Magnetic and Modular Jacks/Plugs</u>

Performance Category 3
Power over Ethernet (PoE) N/A

Product Name Modular Jack 8/8, RJ45

UPC 800756060033

Physical

Color - Resin Black
Durability (mating cycles max) 500
Flammability 94V-0
Inverted / Top Latch No
Jack Height 13.45mm
Lightpipes/LEDs None

Material - Metal Brass, Phosphor Bronze

Material - Plating Mating Gold Material - Plating Termination Tin

Material - Resin High Temperature Thermoplastic

Net Weight 4.005/g

Orientation Right Angle (Side Entry)

PCB Locator Yes
PCB Retention None
PCB Thickness - Recommended 1.60mm

Packaging Type Embossed Tape on Reel

Panel Mount N/A Pitch - Mating Interface 1.02mm Pitch - Termination Interface 1.27mm Plating min - Mating 1.270µm Plating min - Termination 2.540µm Port Configuration 1x1 Positions / Loaded Contacts 8/8 Surface Mount Compatible (SMC) N/A

Temperature Range - Operating -40° to +80°C
Termination Interface: Style Surface Mount

Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 1.5A Grounding to Panel Yes



EU ELV

Not Relevant

EU RoHS China RoHS

Compliant REACH SVHC Not Contained Per -D(2021)4569-DC (8 July 2021)

Halogen-Free

Status Low-Halogen

For more information, please visit Contact US

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

44282 Series

Mates With FCC 68 Plugs

Shielded Yes Voltage - Maximum 125V

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

O01

Process Temperature max. C

235

Material Info

Reference - Drawing Numbers

Packaging Specification PK-70873-700+-001
Product Specification PS-43743-0001-001

Sales Drawing SD-44282-001-001, SD-44282-001-002

This document was generated on 09/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION