
ASSR-1218 , ASSR-1219 and ASSR-1228

Form A, Solid State Relay (Photo MOSFET) ($60V/0.2A/10\Omega$)



Data Sheet



Description

The ASSR-12XX Series consists of an AlGaAs infrared light-emitting diode (LED) input stage optically coupled to a high-voltage output detector circuit. The detector consists of a high-speed photovoltaic diode array and driver circuitry to switch on/off two discrete high voltage MOSFETs. The relay turns on (contact closes) with a minimum input current of 3mA through the input LED. The relay turns off (contact opens) with an input voltage of 0.8V or less.

The single channel configurations, ASSR-1218 and ASSR-1219, are equivalent to 1 Form A Electromechanical Relays (EMR), and the dual channel configuration, ASSR-1228, is equivalent to 2 Form A EMR. They are available in 4-pin SO, 6-pin DIP, 8-pin DIP and Gull Wing Surface Mount for DIP packages. ASSR-1219 enables AC/DC and DC-only output connections. For DC-only connection, the output current, lo, increases to 0.4A and the on-resistance, R(ON) reduces to 2.5 Ω .


Applications

- Telecommunication Switching
- Data Communications
- Industrial Controls
- Medical
- Security
- EMR / Reed Relay Replacement

Features

- Compact Solid-State Bi-directional Signal Switch
- Single and Dual Channel Normally-off Single-Pole-Single-Throw (SPST) Relay
- 60V Output Withstand Voltage
- 0.2A or 0.4A Current Rating (See Schematic for ASSR-1219 Connection A and B)
- Low Input Current: CMOS Compatibility
- Low On-Resistance: 0.25Ω Typical for DC-only, 1Ω Typical for AC/DC
- High Input-to-Output Insulation Voltage (Safety and Regulatory Approved)
 - 3750 Vrms for 1 min per UL1577
 - CSA Component Acceptance

Functional Diagram



¹ Form A in 4-Pin SO Package

CAUTION: It is advised that normal static precautions be taken in handling and assembly of this component to prevent damage and/or degradation which may be induced by ESD.

Ordering Information

ASSR-12xx is UL Recognized with 3750 Vrms for 1 minute per UL1577 and is approved under CSA Component Acceptance Notice #5, File CA 88324.

	Option						
Part number	RoHS Compliant	Package	Surface Mount	Gull Wing	Tape & Reel	Quantity	
	-003E	50 A	Х			100 units per tube	
ASSR-1218	-503E	- SO-4	Х		Х	1500 units per reel	
	-001E					50 units per tube	
ASSR-1219	-301E	300mil DIP-6	Х	Х		50 units per tube	
	-501E		Х	Х	Х	1000 units per reel	
	-002E					50 units per tube	
ASSR-1228	-302E		Х	Х		50 units per tube	
	-502E		Х	Х	Х	1000 units per reel	

Note:- option x2xE for UL1577 5000Vrms for 1minute will be offered upon request

To order, choose a part number from the part number column and combine with the desired option from the option column to form an order entry.

Example 1:

ASSR-1219-501E to order product of 300mil DIP-6 Gull Wing Surface Mount package in Tape and Reel packaging and RoHS Compliant.


Example 2:

ASSR-1228-002E to order product of 300mil DIP-8 package in tube packaging and RoHS Compliant.


Option datasheets are available. Contact your Avago sales representative or authorized distributor for information.


System Schematics

ASSR-1218




ASSR-1219 Connection A







ASSR-1219 Connection B




ASSR-1228






Package Outline Drawings




ASSR-1218 4-Pin Small Outline Package

DIMENSIONS IN MILLIMETERS AND [INCHES] OPTION NUMBER 500 AND UL RECOGNITION NOT MARKED







DIMENSIONS IN MILLIMETERS AND (INCHES).




ASSR-1219 6-Pin DIP Package with Gull Wing Surface Mount Option 300


NOTE: FLOATING LEAD PROTRUSION IS 0.25 mm (10 mils) MAX.








DIMENSIONS IN MILLIMETERS AND (INCHES). OPTION NUMBERS 300 AND 500 NOT MARKED.



ASSR-1228 8-Pin DIP Package with Gull Wing Surface Mount Option 300

NOTE: FLOATING LEAD PROTRUSION IS 0.25 mm (10 mils) MAX.

Lead Free IR Profile



 $T_{smax} = 200^{\circ}C, T_{smin} = 150^{\circ}C$

Non-halide flux should be used

Regulatory Information

The ASSR-1218, ASSR-1219 and ASSR-1228 are approved by the following organizations:

UL

Approved under UL 1577, component recognition program up to $V_{ISO} = 3750 V_{RMS}$ and $5000V_{RMS}$ for option x2xE. Approved under CSA Component Acceptance Notice #5.

Insulation and Safety Related Specifications

Parameter	Symbol	ASSR-1218	ASSR-1219 ASSR-1228	Units	Conditions
Minimum External Air Gap (Clear- ance)	L(101)	4.9	7.1	mm	Measured from input terminals to output terminals, shortest distance through air.
Minimum External Tracking (Creepage)	L(102)	4.9	7.4	mm	Measured from input terminals to output terminals, shortest distance path along body.
Minimum Internal Plastic Gap (Internal Clearance)		0.08	0.08	mm	Through insulation distance conductor to conductor, usually the straight line distance thickness between the emitter and detector.
Tracking Resistance (Comparative Tracking Index)	CTI	175	175	V	DIN IEC 112/VDE 0303 Part 1
Isolation Group (DIN VDE0109)		Illa	Illa		Material Group (DIN VDE 0109)

Absolute Maximum Ratings

Parameter		Symbol	Min.	Max.	Units	Note
Storage Temperature		Ts	-55	125	°C	
Operating Temperature		T _A	-40	85	°C	
Junction Temperature		Tj		125	°C	
Lead Soldering Cycle	Temperature			260	°C	
	Time			10	S	
Input Current	Average	IF		25	mA	
	Surge	_		50		
	Transient			1000		
Reversed Input Voltage		V _R		5	V	
Input Power Dissipation	ASSR-1218	P _{IN}		40	mW	
	ASSR-1219	P _{IN}		40	mW	
	ASSR-1228	P _{IN}		80	mW	
Output Power Dissipation	ASSR-1218	P _O		400	mW	
	ASSR-1219	P _O		400	mW	
	ASSR-1228	P _O		800	mW	
Average Output Current		Io		0.20	А	1
$(T_A = 25^{\circ}C, T_C \le 100^{\circ}C)$	ASSR-1219 Connection B	IO		0.40	А	1
Output Voltage ($T_A = 25^{\circ}C$)		Vo	-60	60	V	2
	ASSR-1219 Connection B	Vo	0	60	V	
Solder Reflow Temperature Pre	ofile	See Lead F	ree IR Profile			

Recommended Operating Conditions

Parameter	Symbol	Min.	Max.	Units	Note
Input Current (ON)	I _{F(ON)}	3	20	mA	3
Input Voltage (OFF)	V _{F(OFF)}	0	0.8	V	
Operating Temperature	T _A	-40	+85	°C	

Package Characteristics

Unless otherwise specified, $T_A = 25^{\circ}C$.

Parameter	Sym.	Min.	Тур.	Max.	Units	Conditions	Note
Input-Output Momentary Withstand Voltage	V _{ISO}	3750			Vrms	RH ≤ 50%, t = 1 min	4, 5
Input-Output Resistance	R _{I-O}		10 ¹²		Ω	$V_{I-O} = 500 Vdc$	
Input-Output Capacitance	ASSR-1218 C _{I-O}		0.4		pF	f = 1 MHz; V _{I-O} = 0 Vdc	4
	ASSR-1219 C _{I-O}		0.5		pF	f = 1 MHz; V _{I-O} = 0 Vdc	
	ASSR-1228 C _{I-O}		0.8		pF	f = 1 MHz; V _{I-O} = 0 Vdc	

Electrical Specifications (DC)

For operating $T_A = +25^{\circ}C$

Parameter	Sym.	Min.	Тур.	Max.	Units	Conditions	Fig.	Note
Output Withstand Voltage	VO(OFF)	60	65		V	V_F =0.8V, I_O =250 µA	5	
Output Leakage Current	I _{O(OFF)}		0.005	1	μA	V _F =0.8V, V _O =60V		
Input Reverse Breakdown Voltage	V _R	5			V	$I_R = 10 \ \mu A$		
Input Forward Voltage	V _F	1.1	1.3	1.6	V	I _F =5mA	6, 7	
Output On-resistance	R _(ON)		1	10	Ω	I _F =5mA, I _O =200mA, Pulse ≤30ms	8, 9	6
	ASSR-1219 Connection B		0.25	2.5	Ω	I _F =5mA, I _O =400mA, Pulse ≤30ms		

Switching Specifications (AC)

For operating $T_A = +25^{\circ}C$

Parameter	Sym.	Min.	Тур.	Max.	Units	Conditions	Fig.	Note
Turn On Time	T _{ON}		0.7	5.0	ms	I _F =5mA, I _O =200mA		
Turn Off Time	T _{OFF}		0.04	5.0	ms	I _F =5mA, I _O =200mA,		

Notes:

1. For derating, refer to Figure 1, 2, 3 and 4.

2. The voltage across the output terminals of the relay should not exceed this rated withstand voltage. Over-voltage protection circuits should be added in some applications to protect against over-voltage transients.

3. Threshold to switch device is $I_F \ge 0.5$ mA, however, for qualified device performance over temperature range, it is recommended to operate at $I_F = 5$ mA.

4. Device is considered as a two terminal device:

ASSR-1218 - pin 1, 2 shorted and pin 3, 4 shorted.

ASSR-1219 - pin 1, 2, 3 shorted and pin 4, 5, 6 shorted.

ASSR-1228 - pin 1, 2, 3, 4 shorted and pin 5, 6, 7, 8 shorted.

5. The Input-Output Momentary Withstand Voltage is a dielectric voltage rating that should not be interpreted as an input-output continuous voltage rating. For the continuous voltage rating refer to the IEC/EN/DIN EN 60747-5-2 Insulation Characteristics Table (if applicable), your equipment level safety specification, or Avago Technologies Application Note 1074, "Optocoupler Input-Output Endurance Voltage."


6. During the pulsed $R_{(ON)}$ measurement (I_O duration \leq 30ms), ambient (T_A) and case temperature (T_C) are equal.

Application Information

On-Resistance and Derating Curves

The Output On-Resistance, $R_{(ON)}$, specified in this data sheet, is the resistance measured across the output contact when a pulse current signal (lo=200mA) is applied to the output pins. The use of a pulsed signal (\leq 30ms) implies that each junction temperature is equal to the ambient and case temperatures. The steady-state resistance, Rss, on the other hand, is the value of resistance measured across the output contact when a DC current signal is applied to the output pins for a duration sufficient to reach thermal equilibrium. Rss includes the effects of the temperature rise in the device.

Figure 1, 2, 3 and 4 specify the maximum average output current allowable for a given ambient temperature. The maximum allowable output current and power dissipation are related by the expression Rss = $Po(max)/(lo(max))^2$ from which Rss can be calculated. Staying within the safe area assures that the steady state MOS-FET junction temperature remains less than 125 °C.









Figure 3. Maximum Output Current Rating vs Ambient Temperature (ASSR-1219-001E DC Connection)









Figure 4. Maximum Output Current Rating vs Ambient Temperature (ASSR-1228-002E)






Figure 5. Normalized Output Withstand Voltage vs Temperature




Figure 7. Typical Forward Current vs Forward Voltage





Figure 6. Typical Forward Voltage vs Temperature






Figure 9. Typical Output Current vs Output Voltage

For product information and a complete list of distributors, please go to our web site: www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies Limited in the United States and other countries. Data subject to change. Copyright © 2005-2008 Avago Technologies Limited. All rights reserved. AV02-0173EN - May 5, 2008

