Turbine flow meter

Stand Alone or Complete Systems with Signal Conditioning


FTB-100 Series



- Accuracy
- ✓ Ball Bearing Design for Economy
- ✓ Non-Metallic Bearing **Retainers for Long Life**
- Replacement Bearings Field Installable Without Loss of Calibration
- Disassembles Quickly for Easy Maintenance
- Deflector Cones Stabilize **Low Mass Rotor for Increased Bearing Life**
- and Scaled Frequency **Outputs Available**

The FTB-100 Series of turbine meters have a shielded ball bearing design for high-accuracy performance (±0.5% of reading, not full scale) at an economical cost. The non-metallic bearing retainers minimize friction, thereby allowing these meters to be used with clean fluids that have poor lubricating properties (i.e., water). Ball bearings also give the widest linear flow range, particularly in larger turbines. Bearing replacement and clean-up are fast and easy, since all internal parts are easily accessible by removing a single nut.

These turbine flow meters have a low mass rotor design which allows rapid dynamic response, so they can be used in pulsating flow applications.



Deflector cones eliminate downstream thrust on the rotor and allow hydrodynamic positioning of the rotor between the cones. This provides wider rangeability and longer bearing life than conventional turbine flow meters. Integral flowstraightening tubes minimize the effects of upstream turbulence.

FTB-100 Turbine Meters are available with integral signal conditioners which provide scaled and unscaled frequencies. 4 to 20 mA, or 0 to 5 volt outputs

Units without integral signal conditioners are supplied with mating connector for two-wire hook-up.

SPECIFICATIONS

Accuracy: ±0.5% of reading Repeatability: ±0.1% of reading **Maximum Temperature Range:** -268 to 232°C (-450 to 450°F) **Maximum Intermittent Overrange:**

150% of maximum range

Minimum Output Amplitude: 30 mV Peak-to-Peak unscaled pulse

Materials of Construction: Body: 304 stainless steel

Rotor: 17-4 PH steel Bearings: Ceramic

Minimum straight pipe requirements: 10 pipe diameters upstream, 5 downstream

Economical Ball Bearing Design with NPT End Fittings



Complete The System

SIGNAL CONDITIONERS 4 to 20 mA, amplified pulse, or 0 to 5 Vdc.

SELECT 1 OR 2

DISPLAY, ALARM, CONTROL DPF60

Pulse output and voltage

or current output.

2 DISPLAY, TOTALIZE, AND BATCH CONTROL

Scaled pulse or current output DPF701.

NIST Calibration for Other Viscosity Liquids*

	Viscosity Range		
Meter Size	0.6 to 99 cSt	100 to 299 cSt	
FTB-101 thru 106 ½ thru 1"			
FTB-107 thru 109 11/4 thru 2"	Additional cost		
FTB-110 thru 111 2½ thru 3"			

^{*} Standard NIST calibration is for water (viscosity = 1 cSt)

To Order							
Turbine Meter Only Model No.†	Linear Flow Range for Water LPM (GPM)	MNPT End Fittings	Maximum Operating Pressure (psig)	Maximum Pressure Drop (psid)	Length mm (inch)	Nominal K-Factor (Pulses/Gallon)	Weight kg (lb)
FTB-101	1.32 to 13.2 (0.35 to 3.5)	1/2	5000	3.0	62 (2.45)	13,000	0.4 (1)
FTB-102	2.84 to 28.4 (0.75 to 7.5)	1/2	5000	5.0	62 (2.45)	10,000	0.4 (1)
FTB-103	4.73 to 36.0 (1.25 to 9.5)	1/2	5000	5.2	62 (2.45)	6000	0.4 (1)
FTB-104	6.62 to 61 (1.75 to 16)	3/4	5000	3.0	70 (2.75)	4100	0.4 (1)
FTB-105	9.5 to 110 (2.5 to 29)	3/4	4250	5.0	83 (3.25)	2200	0.4 (1)
FTB-106	15 to 227 (4 to 60)	1	3850	5.1	89 (3.50)	640	0.9 (2)
FTB-107	23 to 352 (6 to 93)	1 1⁄4	3850	4.3	99 (3.88)	410	0.9 (2)
FTB-108	30 to 492 (8 to 130)	1 ½	3000	3.0	111 (4.38)	230	1.4 (3)
FTB-109	57 to 852 (15 to 225)	2	2500	3.3	121 (4.75)	120	1.8 (4)
FTB-110	95 to 1514 (25 to 400)	2½	2250	4.0	154 (6.06)	62	2.3 (5)
FTB-111	151 to 2460 (40 to 650)	3	2000	4.0	191 (7.50)	55	3.2 (7)

Comes complete with operator's manual and 10-point NIST calibration certificate for water.

Ordering Examples: FTB-101, ½ NPT turbine meter with standard NIST calibration for 1 cSt viscosity.

FTB-106, 1 NPT turbine meter with NIST calibration for 5 cSt viscosity liquid.

[†] Complete systems with signal conditioner available, consult sales.

INTEGRAL OR REMOTE SIGNAL CONDITIONER

FLSC-C1-LIQ



- ✓ Loop Powered 4 to 20 mA
- ✓ Signal Linearization
- ✓ Factory Configuration Available
- ✓ Windows® Configuration Software*

The FLSC-C1-LIQ is a microprocessor controlled 2-wire 4 to 20 mA transmitter. The FLSC-C1-LIQ converts a low level, frequency signal from a flow sensor into an analog 4 to 20 mA output. The output is proportional to the flow rate. The FLSC-C1-LIQ is designed for integral mounting to the FTB-100, FTB-200 and FTB-400 Series** liquid turbines.

** Visit OMEGA for details.

SPECIFICATIONS

Input Signal Type: Magnetic pickup Input Frequency Range: 0.2 Hz to 4 KHz Signal Level: 10 mV rms to 30 Vdc Power Supply: Loop power 10 to 30 Vdc

Reverse polarity protected **Loop Burden Voltage:** 8.5V **Analog Output:** 4 to 20 mA 24 mA overflow condition

Load Resistance: Maximum 650 $\boldsymbol{\Omega}$


at 24 Vdc

Accuracy: ±0.02% of full scale Temperature Drift: 40 ppm/degree C Communications: RS232 port for configuration and diagnostics Operating Temperature: -40 to 85°C (-40 to 185°F)

Humidity: 0 to 90% non-condensing Enclosure: Extruded Aluminum Explosion-Proof ATEX enclosure Regulatory: CE Compliant Up to 20 point linearization Windows Configuration Software*

(cable sold separately)





Enclosure meets Class I, Div 1 & 2, Groups A, B, C & D. Class 1, Zones 1 & 2, Groups IIB + H2 IIA. Class II, Div 1 & 2 Groups E, F & G. Class III. NEMA 3, 4, 7(B, C, D) 9(E, F, G). Cenelec EEx d IIC IP66, UL, CSA, FM Approved. ATEX Certified.

To Order		
Model No.	Description	
FLSC-C1-LIQ	Loop-powered signal conditioner, 4 to 20 mA, CE/ATEX	
OM-CONV-USB	USB to RS232 converter	
FLSC-C-CABLE	Molex to 9-pin "D" connector	

Comes complete with operator's manual and enclosure.

Ordering Example: FLSC-C1-LIQ, loop-powered turbine signal conditioner in ATEX enclosure with FLSC-C-CABLE Molex to 9-pin "D" connector.

^{*} Available free at omega.com/ftp

INTEGRAL OR REMOTE SIGNAL CONDITIONER

FLSC-C3-LIQ



- ✓ DC or AC Powered
- ✓ Pulse and Analog Outputs
- (Optional)
- ∠ 20 Point Linearization
- ✓ Factory Configuration Available
- ✓ Windows® Configuration Software*



The FLSC-C3-LIQ is a DC powered, microprocessor controlled transmitter. It outputs a pulse scaled per unit of flow, and analog signal proportional to flow rate.

The FLSC-C3-LIQ-AL can be configured with high or low alarms. The FLSC-C3-LIQ is designed for integral mounting to the FTB-100, FTB-200 and FTB-400 Series* liquid turbines.

SPECIFICATIONS

Input Signal Type: Magnetic pickup, MCP pickup, contact closure, pulse Input Frequency Range: 0.2 Hz to 4 KHz Signal Level: 10 mV rms to 30 Vdc

Power Supply: 13 to 30 Vdc reverse

polarity protection

Analog Output: 4 to 20 mA, 1 to 5V

24 mA overflow condition

Load Resistance: Maximum 650 Ω at

24 Vdc

Accuracy: ±0.02% of full scale Temperature Drift: 40 ppm/degree C Pulse Output: 0 to 5V, 0 to 10V, open collector, AC square. Internal pull up 10 kΩ. Recommended minimum

load resistance 50 k Ω

Pulse Scaling: Divide by 1, 10 or 100 per

flow unit


Hi/Lo Alarm (-AL Model) Optional: Relay (2A, 30 Vdc), 0 to 5V, open

collector (0.5A, 30V)

Communications: RS232 port for configuration and diagnostics

Operating Temperature: -40 to 85°C

(-40 to 185°F)



Enclosure meets Class I, Div 1 & 2, Groups A, B, C & D. Class 1, Zones 1 & 2, Groups IIB + H2IIA. Class II, Div 1 & 2 Groups E, F & G. Class III. NEMA 3, 4 7(B, C, D) 9(E, F, G). Cenelec EEx d IIC IP66, UL, CSA, FM Approved. ATEX Certified.

Humidity: 0 to 90% non-condensing Enclosure: Extruded aluminum

explosion-proof ATEX

Regulatory: CE Compliant up to 20 point linearization Windows Configuration Software* (cable sold separately)

To Order		
Model No.	Description	
FLSC-C3-LIQ	DC powered signal conditioner 4 to 20 mA, CE ATEX	
FLSC-C3-AL-LIQ	DC powered signal conditioner 4 to 20 mA, alarm CE ATEX	
OM-CONV-USB	USB to RS232 converter	
FLSC-C-CABLE	Molex to 9-pin "D" connector	

Comes complete with operator's manual and enclosure.

Ordering Example: FLSC-C3-LIQ, DC powered turbine signal conditioner with FLSC-C-CABLE Molex to 9-pin "D" connector.

^{**} Visit OMEGA for details.

^{*} Available free at omega.com/ftp