



- Robust aluminium housing including wire guard
- Extreme durability thanks to low wear belt drive
- Salt water resistant
- Extremely quiet
- Installation without the need to disassemble the mechanism
- Robust bracket made of V2A stainless steel (accessory)

**i TECHNICAL SPECIFICATIONS:**

Dimensions (Ø x Height):	153 mm x 198 mm
Housing:	Black laquered aluminium with integral wire guard
Lens:	PC, transparent
Fixing:	Base mounting
Connection:	Screw terminal with wire protection max. 2.5 mm <sup>2</sup>
Cable entry:	Cable gland M20 x 1.5 mm (included in assembly) Cable diameter 6-13 mm
Installation position:	As required
Halogen bulb:	G 6.35 20 W 12/24 V
Mirror rotating rate:	C. 180 r.p.m.
Service life of drive:	> 5.000 hrs



**🛒 ORDER SPECIFICATIONS:**

Voltage	24 V AC/DC	115 V AC / 115 V DC	/ 230 V AC / 230 V DC
Current consumption	1.0 A	0.35 A	/ 0.5 A / 0.15 A / 0.1 A
red	<b>839 160 75</b>	<b>839 160 78</b>	
yellow	<b>839 360 75</b>	<b>839 360 78</b>	

**🏠 ACCESSORIES:**

Mounting bracket	<b>975 839 02</b>
------------------	-------------------

**🔧 SPARE PARTS:**

Halogen bulb 20 W/12 V for 115 V AC/DC, 230 V AC	<b>955 885 24</b>
--	-------------------

Halogen bulb 20 W/24 V for 24 V AC/DC	<b>955 885 25</b>
---------------------------------------	-------------------

**📐 TECHNICAL DIAGRAMS:**

see page 317



Also suitable for use in rough conditions



Mounting bracket (accessory)

Sizes of Rotating Beacons



See note on page 347

