



Main

Range	9002AW
Product	Foot switch
Contact Operation	2 steps
Certifications	UL Listed CSA
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT per step
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Oversized pedal shield Safety door Side shield
Operator Action	Spring return
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508 10 A 240 V AC inductive control circuit UL 508 6 A 480 V AC inductive control circuit UL 508 5 A 600 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 0.5 A 125 V DC resistive control circuit UL 508
Height	6.26 in (159 mm)
Width	6.42 in (163 mm)
Depth	8.54 in (217 mm)



Ordering and shipping details

Category	21441 - 9002 AW FOOT SWITCHES
Discount Schedule	CS1
GTIN	00785901652434
Nbr. of units in pkg.	1
Package weight(Lbs)	11.66 lb(US) (5.29 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	15.24 in (38.710 cm)
Package 1 width	6.00 in (15.240 cm)
Package 1 Length	38.71 in (98.322 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
