

# Product datasheet

Specifications



Foot Switch, Harmony, industrial, unshielded, two stage, 5A at 600 VAC, SPDT contact each stage, NEMA 2, 4, 13 enclosure

9002AW5

## Main

Range	9002AW
Product	Foot switch
Contact Operation	2 steps
Certifications	CSA UL listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT per step
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Unshielded
Operator Action	Spring return
Rated Breaking Capacity	15 A at 120 V AC for inductive control circuit conforming to UL 508 10 A at 240 V AC for inductive control circuit conforming to UL 508 6 A at 480 V AC for inductive control circuit conforming to UL 508 5 A at 600 V AC for inductive control circuit conforming to UL 508 15 A at 120 V AC for resistive control circuit conforming to UL 508 0.5 A at 125 V DC for resistive control circuit conforming to UL 508
Height	99 mm
Width	114 mm
Depth	216 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.465 kg
Package 1 Height	8.382 cm
Package 1 width	12.192 cm
Package 1 Length	22.86 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

---

<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a>
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

---

### **Contractual warranty**

---

<b>Warranty</b>	18 months
-----------------	-----------

---