AUTOMOTIVE

RoHS

COMPLIANT

HALOGEN

FREE



Vishay General Semiconductor

Surface-Mount TMBS® (Trench MOS Barrier Schottky) Rectifier



Cathode O Anode

LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS				
I _{F(AV)}	5.0 A			
V _{RRM}	60 V			
I _{FSM}	100 A			
V _F at I _F = 5.0 A (125 °C)	0.54 V			
T _J max.	175 °C			
Package	SlimSMA (DO-221AC)			
Circuit configuration	Single			

FEATURES

- Very low profile typical height of 0.95 mm
- · Ideal for automated placement
- Trench MOS Schottky technology
- · Low power losses, high efficiency
- · Low forward voltage drop
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 - Automotive ordering code: base P/NHM3
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in high frequency inverters, freewheeling, DC/DC converters, and polarity protection in commercial, industrial, and automotive applications.

MECHANICAL DATA

Case: SlimSMA (DO-221AC)

Molding compound meets UL 94 V-0 flammability rating

Base P/N-M3 - halogen-free, RoHS-compliant

Base P/NHM3 - halogen-free, RoHS-compliant, and AEC-Q101 gualified

ALC-Q TO I qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)				
PARAMETER	SYMBOL	VSSAF5M63	UNIT	
Device marking code		5M63		
Maximum repetitive peak reverse voltage	V_{RRM}	60	V	
Maximum DC forward current	I _{F(AV)} (1)	2.6	- A	
Maximum DC forward current	I _{F(AV)} (2)	5.0		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	100	А	
Operating junction temperature range	T _J ⁽³⁾	-40 to +175	°C	
Storage temperature range	T _{STG}	-55 to +175	°C	

Notes

- (1) Free air, mounted on recommended copper pad area
- (2) Mounted on 30 mm x 30 mm pad area
- $^{(3)}$ The heat generated must be less than thermal conductivity from junction-to-ambient: $dP_D/dT_J < 1/R_{\theta JA}$



www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _J = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT
Instantaneous forward voltage	I _F = 2.5 A	$T_J = 25 ^{\circ}\text{C}$	V _F ⁽¹⁾	0.53	-	V
	I _F = 5.0 A			0.60	0.66	
	$I_F = 2.5 A$	T _J = 125 °C		0.44	-	
	I _F = 5.0 A			0.54	0.6	
Reverse current	V _R = 60 V	T _J = 25 °C	I _R ⁽²⁾	-	0.01	mA .
	v _R = 60 v	T _J = 125 °C	IR (=)	0.5	2	IIIA
Typical junction capacitance	4.0 V, 1 MHz		CJ	700	-	pF

Notes

 $^{(1)}\,$ Pulse test: 300 μs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width ≤ 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise specified)				
PARAMETER SYMBOL VSSAF5M63				
Typical thermal resistance	R ₀ JA (1)(2)	115	°C/W	
	R _{0JM} (3)	12		

Notes

 $^{(3)}$ Free air, mounted on recommended PCB, 2 oz. pad area; thermal resistance $R_{\theta JA}$ - junction to ambient

 $^{(4)}$ The heat generated must be less than thermal conductivity from junction-to-ambient: $dP_D/DT_J < 1/R_{\theta JA}$

 $^{(5)}$ Mounted on 30 mm x 30 mm pad area, $R_{\theta JM}$ - junction to mount

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
VSSAF5M63-M3/H	0.032	Н	3500	7" diameter plastic tape and reel	
VSSAF5M63-M3/I	0.032	I	14 000	13" diameter plastic tape and reel	
VSSAF5M63HM3/H (1)	0.032	Н	3500	7" diameter plastic tape and reel	
VSSAF5M63HM3/I (1)	0.032	L	14 000	13" diameter plastic tape and reel	

Note

(1) AEC-Q101 qualified



Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 5 - Typical Junction Capacitance




Fig. 6 - Typical Transient Thermal Impedance

0.047 (1.20)

MIN.

Vishay General Semiconductor




Fig. 7 - Thermal Resistance Junction to Ambient vs. Copper Pad Area

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

Cathode Band 0.106 (2.70) 0.057 (1.45) 0.098 (2.50) 0.049 (1.25) 0.171 (4.35) 0.047 (1.20) Typ.: 0.019 (0.48) 0.163 (4.15) 0.030 (0.75) 0.211 (5.35) 0.199 (5.05) **Mounting Pad Layout** 0.039 (1.00) 0.035 (0.90) 0.060 (1.52) 0.012 (0.30) MIN. 0.006 (0.15)

0.047 (1.20)

MIN.

SlimSMA (DO-221AC)

0.123 (3.12) MAX.

0.217 (5.52) REF.



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.