

Infrared Thermometer



- Dual laser pointers converge to a single spot when the unit is at the optimal distance from the object being measured
- Use the dual laser to focus on the target, pull the trigger and "shoot"
- Wide temperature range from -50° to +650°C
- Measures °C, °F
- Distance to spot size ratio is 8:1 at the focal point
- Impact-resistant double moulded ABS case
- Adjustable emissivity 0.10 to 1.0
- Response time less than 150 milliseconds
- Large backlit LCD display with function indicators
- Automatic data hold when trigger released
- Max display
- High and low alarm
- Trigger lock for continuous use
- Auto power off
- Over range indication
- Supplied with carry case and battery
- CAL-IR Calibration Certificate Issued at 5 points: 25°C, 50°C, 75°C, 100°C & 150°C.

Technical Specifications

Range	-50° to +650°C (-58° to +1202°F)
Resolution	0.1°C/F
Accuracy	±1.0% of reading
Power	1 x 9V PP3 battery
Dimensions	146 x 104 x 43mm
Weight	63g

Model No Description

IR-8862	Dual Laser Infrared Thermometer
CAL-IR	Calibration Certificate
LR-61	V PP3 Alkaline Battery

Global Measurement and Control Limited
PO Box 1
Derwent Street, Long Eaton
Nottingham NG10 3LP

Telephone: 0115 946 7441 • Fax: 0115 946 7442
e-mail: enquiries@globaltd.co.uk
website: www.globaltd.co.uk

Company Registration No. 4918028
Registered Address: Trent Mills, Long Eaton, Nottinghamshire NG10 3LP

A member of the Concord Holdings Group