

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638236700](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for Crimp Terminal

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above. Type: 4D
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	884982279957
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight 317.100/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents [ATS-638236700-001](#)



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129](#) Series

Application Tooling | [FAQ](#)

Description | **Product #**

Milli-Grid Crimp Terminal, Chain, 0.38µm Select Gold, Lead free [873968051](#)

2mm MGrid Crimp Term WtB Chain Unpl [873968999](#)

Milli-Grid Crimp Terminal, Chain, 0.75µm Select Gold, Lead free [873969051](#)

0.38µm Select Gold, Lead free

2mm MGrid Crimp Term WtB Chain Unpl

Milli-Grid Crimp Terminal, Chain, 0.75µm Select Gold, Lead free

0.75µm Select Gold, Lead free

0.38µm Select Gold, Lead free

0.75µm Select Gold, Lead free

0.38µm Select Gold, Lead free