

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638258400](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Hand Tool for MX64 ISO Terminal

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)


**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	Die sets are not sold separately; the complete hand tool needs to be ordered to obtain the die set. Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	887191247755
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**  
[Application Tooling Documents](#)

ATS-6382584HM-001, TM-638000029-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[207129](#) Series

**Use With**

[33467](#) , [33468](#) , [34736](#) MX64 ISO Terminal, 0.35mm<sup>2</sup> and 0.50-0.75mm<sup>2</sup> wire

**Application Tooling**

**Description**

**FAQ**

**Product #**

2.54mm Pitch [334670021](#)

MX64 Terminal, Gold (Au) Plating, 0.35mm<sup>2</sup> Wire, Left ReelPayoff, Also used with MX123

Female Receptacle Housing

2.54mm Pitch MX64 [334670022](#)

Terminal, Gold (Au) Plating, 0.35mm<sup>2</sup> Wire, Right Reel Payoff, Also used with MX123 Female

Receptacle Housing

2.54mm Pitch [334670023](#)

MX64 Terminal, Gold (Au) Plating,

0.50-0.75mm<sup>2</sup> Wire,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch 334670024

MX64 Terminal,  
Gold (Au) Plating,  
0.50-0.75mm<sup>2</sup>  
Wire, Right Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334680021

Terminal, Tin (Sn)  
Plating, 0.35mm<sup>2</sup>  
Wire, Left Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334680022

Terminal, Tin (Sn)  
Plating, 0.35mm<sup>2</sup>  
Wire, Right Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch 334680023

MX64 Terminal,  
Tin (Sn) Plating,  
0.50-0.75mm<sup>2</sup> Wire,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch 334680024

MX64 Terminal,  
Tin (Sn) Plating,  
0.50-0.75mm<sup>2</sup>  
Wire, Right Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 347360025

Terminal, Silver  
Plating, 0.35mm<sup>2</sup>,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 347360026

Terminal, Silver  
Plating, 0.35mm<sup>2</sup>,  
Right Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch 347360027

MX64 Terminal,  
Silver Plating,  
0.50-0.75mm<sup>2</sup>, Left  
Reel Payoff, Also  
used with MX123  
Female Receptacle  
Housing

2.54mm Pitch 347360028  
MX64 Terminal,  
Silver Plating,  
0.50-0.75mm<sup>2</sup>, Right  
Reel Payoff, Also  
used with MX123  
Female Receptacle  
Housing

This document was generated on 11/02/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**