


TE Internal #: TB1147D4722-005 M8/M12 Cable Assemblies, Sensor/Actuator, 4 Position, M8 Plug, M8 Pigtail, Straight Connector Orientation (End A) View on TE.com >



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies



M8/M12 Application Type: Sensor/Actuator

Number of Positions: 4

Connector Type (End A): M8 Plug

Cable Assembly Type: M8 Pigtail

Connector Orientation (End A): Straight

Features

Product Type Features

LED	Without
Cable Type	PUR
Product Type	Cable Assembly
Assembly Type	Overmolded
Connector Type (End A)	M8 Plug
Cable Assembly Type	M8 Pigtail
Configuration Features	
Number of Positions	4
Mechanical Attachment	
Screw & Hole Thread Size	M8
Connector Orientation (End A)	Straight
Connector Orientation (End B)	Straight
Housing Features	
Housing Material	Nylon
Operation/Application	

C For support call+1 800 522 6752

TB1147D4722-005

M8/M12 Cable Assemblies, Sensor/Actuator, 4 Position, M8 Plug, M8 Pigtail, Straight Connector Orientation (End A)



M8/M12 Application Type	Sensor/Actuator
Shielded	Yes
Other	
Cable Assembly Length	5 m
Cable Assembly Configuration	Double Ended
Product Compliance For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (1.2% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

TB1147D4722-005

M8/M12 Cable Assemblies, Sensor/Actuator, 4 Position, M8 Plug, M8 Pigtail, Straight Connector Orientation (End A)



TE Part # T4040110044-000 RPC-SPE-M8-FF-4CON-LBUS

Documents

Product Drawings RPC-M8-MS-MS-4CON-P-5.0SH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_TB1147D4722-005_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_TB1147D4722-005_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_TB1147D4722-005_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages Catalog-Single Pair Ethernet M8 Hybrid Board Receptacle IP67 and Single Pair Ethernet M8 Hybrid Cordset

English

Product Specifications Application Specification

English