

KUL-11D15D-110

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield KUL

TE Internal #: 3-1393115-0

Potter & Brumfield KUL, Power Relays, Industrial Panel Plug-In, Bistable, 2 Coils, 1650 mW Coil Power Rating DC, 7400 Ω Coil Resistance

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**
Coil Magnetic System: **Bistable, 2 Coils**
Coil Power Rating Class: **1500 mW**
Coil Power Rating DC: **1650 mW**
Coil Resistance: **7400 Ω**

Features

Product Type Features

Power Relay Type	Industrial Panel Plug-In
------------------	--------------------------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	1000 – 1500 V
Insulation Initial Dielectric Between Contacts & Coil	1500 Vrms
Actuating System	DC
Insulation Initial Dielectric Between Open Contacts	500 Vrms
Contact Limiting Making Current	10 A
Contact Limiting Short-Time Current	10 A
Contact Limiting Continuous Current	10 A
Insulation Initial Dielectric Between Adjacent Contacts	1500 Vrms
Insulation Initial Resistance	100 MΩ
Contact Limiting Breaking Current	10 A
Coil Magnetic System	Bistable, 2 Coils
Coil Power Rating Class	1500 mW
Coil Power Rating DC	1650 mW
Coil Resistance	7400 Ω
Coil Special Features	Magnetic Latching
Coil Voltage Rating	110 VDC



Contact Switching Load (Min)	300mA @ 12V
Contact Voltage Rating	240 VAC

Body Features

Product Weight	96 g[3.386 oz]
----------------	----------------

Contact Features

Contact Arrangement	2 Form C (CO)
Contact Current Class	5 – 10 A, 16 A
Contact Current Rating (Max)	10 A
Contact Material	AgCdO
Contact Number of Poles	2
Relay Terminal Type	Quick Connect, Solder

Mechanical Attachment

Relay Mounting Type	Socket
---------------------	--------

Dimensions

Length Class (Mechanical)	35 – 40 mm
Width Class (Mechanical)	30 – 40 mm
Product Width	35.7 mm[1.405 in]
Product Length	38.9 mm[1.55 in]
Product Height	54.8 mm[2.157 in]

Usage Conditions

Environmental Ambient Temperature Class	0 – 50 °C
Environmental Ambient Temperature (Max)	50 °C[122 °F]
Operating Temperature Range	-45 – 50 °C

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2022
(223)
Candidate List Declared Against: JAN 2021
(211)
SVHC > Threshold:
Cadmium oxide (7.95% in Component Part)
Cadmium oxide (12.06% in Component Part)

Article Safe Usage Statements:
Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-1419106-5 27E893=SOCKET,KU,11,QC,POLY,NA-	 TE Part # 1419106-4 27E046=SOCKET,KU,11,PC,NYL,NAT	 TE Part # 1393143-1 27E043=SOCKET,KU,11,SLG,NYL,N	 TE Part # 1393143-5 27E121=SOCKET,KUP,11,SCW,PLE
 TE Part # 3-1393143-8 27E396=SOCKETS	 TE Part # 1393143-2 27E067=SOCKET,KU,11,QC.187,NY		

Also in the Series | Potter & Brumfield KUL



Customers Also Bought

TE Part #1393143-6
27E122=SOCKET,KRP,8,SCW,PLES

TE Part #2-1419106-3
27E891=SOCKET,KRPA,8,OCTAL,PO

TE Part #2-1419106-4
27E892=SOCKET,KRPA,11,OCTAL,PO

TE Part #9-1393113-7
KUEP-3D15-110=KU

TE Part #1623750-6
ER58 15K 5% AMMO

TE Part #4-1393104-2
KRPA-11DG-110=KRPA

TE Part #5-1393104-1
KRPA-11DN-24=KRPA

TE Part #2-1393115-6
KUL-11A15S-120=KU

TE Part #3-1423159-1
7012PH=RLY,STD,ON,2P,125VDC,30

TE Part #1520204-1
8690K2=10 AMP TOGGLE DPDT

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_3-1393115-0_A.2d_dxf.zip
- English
- Customer View Model
- ENG_CVM_CVM_3-1393115-0_A.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_3-1393115-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KUL 10 Amp Magnetic Latching Relay](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English