

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877011001](#)
Status: **Active**
Overview: Serial ATA Connectors
Description: 1.27mm Pitch Serial ATA Host Receptacle, Press-fit, Vertical, Standard Height, 0.76µm Gold (Au) Selective, 22 Circuits, Lead-Free

Documents:

[3D Model](#) [Product Specification PS-87701-033-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family PCB Receptacles
 Series [87701](#)
 Application Board-to-Board, Signal
 Overview [Serial ATA Connectors](#)
 Product Name Serial ATA
 UPC 822348698981

Physical

(p)ower-(s)ignal Configuration 15p - 7s
 Circuits (Loaded) 22
 Circuits (maximum) 22
 Durability (mating cycles max) 500
 Flammability 94V-0
 Glow-Wire Capable No
 Lock to Mating Part Yes
 Material - Metal Copper
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Net Weight 1.535/g
 Number of Rows 2
 Orientation Vertical
 PC Tail Length 3.45mm
 PCB Locator Yes
 PCB Retention Yes
 PCB Thickness - Recommended 1.52mm, 2.03mm
 Packaging Type Tray
 Pitch - Mating Interface 1.27mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40° to +105°C
 Termination Interface: Style Through Hole


Electrical

Current - Maximum per Contact 1.5A
 Voltage - Maximum 30V

Solder Process Data

Lead-freeProcess Capability N/A

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87701](#) Series

Mates With

[87679](#) , [87799](#) , [87703](#)

Reference - Drawing Numbers

Application Tooling Documents	2002142327-000
Application Tooling Drawing	2002142327-000
Application Tooling Model	2002142327-000
Electrical Model Document	EE-87701-001-001
Product Specification	PS-87701-033-001
Sales Drawing	SD-87701-013-001

This document was generated on 09/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION