

Product information

74 22 250 T

High Leverage Diagonal Cutter

DIN ISO 5749

- Pliers with tether attachment point for mounting a fall protection system
- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- 12° angled head offers clearance for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General	
Article No.	74 22 250 T
EAN	4003773080114
Pliers	black atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	460 g
Dimensions	250 x 51 x 22 mm
Standard	DIN ISO 5749
Reach	no
RohS	no
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 4.6 mm
Cutting capacities hard wire (diameter)	Ø 3.5 mm
Cutting capacities piano wire (diameter)	Ø 3.0 mm
Drop Protection System	yes
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

