

## Product information

# 74 91 250

## High Leverage Centre Cutter



- With integrated forged axle for heavy duty
- With precision cutting edges for soft, hard and piano wire
- Cuts thick wires with less effort than other diagonal cutters of the same length
- Centric precision cutting edges
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



### General

Article No.	74 91 250
EAN	4003773034070
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	395 g
Dimensions	250 x 52 x 16 mm
Reach	no
RohS	no

### Technical details

Cutting capacities soft wire (diameter)	Ø 5 mm
Cutting capacities medium hard wire (diameter)	Ø 5.0 mm
Cutting capacities hard wire (diameter)	Ø 3.8 mm
Cutting capacities piano wire (diameter)	Ø 3.5 mm

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

