

EXTERNAL DESKTOP POWER SUPPLY 24VDC 160WATT

POWERPAX: SW4379D



Features:

- Universal Input
- IEC-320-C14 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,FCC,GS,CE,RCM

Description:

Our range of 160 Watt AC/DC switch mode power supplies provide 160 Watts of continuous output power in a high quality compact enclosure suitable for many general power applications.

Specification	
Part Code	SW4379D
Input Voltage Range	100 → 240 Vac
Input Frequency Range	50 → 60Hz
Input Connector	IEC 320-C14
Input Current Rated	2.2A Max
Inrush Current	100A Max at 240VAC cold start
Leakage Current	<3.5mA
Efficiency	≥88%
Input Power (Output: No Load)	0. 21W (At 230 Vac & At No load)
Output Voltage Rating	24 V
Output Current Range	6.6A Max
Output Min Current	0A
Output Connection Type	4 PIN DIN
Line and Load Regulation	+/-5%
Over Voltage Protection	V out * 150% Max. (Latch)
Over Current Protection	I out * 150% Max. (Auto recovery)
Short Circuit Protection	Shut down
Over Temperature Protection	Shut down
Ripple Voltage	240 mV Max.
Hi-Pot	3000Vac 10mA 1 min.
Safety Approved	CUL,CB,CUL/UL,GS,PSE,BSMI,RCM,CCC
EMI Standard	CE / FCC Class B ; Conduction & Radiation Met.
Operating Temperature Range	0°C → +40 °C
Storage Temperature	-20°C → +80°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Dimensions	175.2(L) x 74(W) x 42(H) mm
Product Weight	700g
Regulator Type	Switched Mode Power Supply


General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

EXTERNAL DESKTOP POWER SUPPLY 24VDC 160WATT

POWERPAX: SW4379D

Diagrams



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

POWERPAX

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500