# Function Generator FG 100

digimess® compact

Order No.: H.UC 65-00



The function generator FG 100 is conceived as a "standard signal source" for daily laboratory use. The wide frequency range from 0.5 Hz to 20 MHz in connection with the signal forms offered and the special functions ensures that a further application field is covered. The internal sweep function allows a direct representation of transmitting curves an ascilloscopes or Y/t recorders. The precise digital frequency setting and the high frequency constancy, which is unusual in this price category, render this function generator interesting even for the most demanding applications. As a versatile signal source, the FG 100 will therefore soon be indispensable to every laboratory technician. Like all devices of the GRUNDIG digimess\* series, the FG 100 has a microprocessor control system providing simple operation by means of the "quattro Key"

operating concept, as well as a self-diagnostics feature and complete remote controllability via the serial RS-232 C interface. The requested parameters such as frequency and signal amplitude are automatically set with the digital rotary switch. The remote controllability via PC interface allows the installation of the FG 100 into automatic test systems of various kinds. The FG 100 thus also fulfills the demands made by industrial companies. By means of the two 16-digit alphanumeric LC display lines with background illumination, you are always informed of all measured values and settings. Due to its excellent price/performance ratio this generator will find wide-spread application in design, production, service and training. This generator should be present in every measuring field.

#### **Technical Data**

#### General Features

Nominal temperature  $+23 \,^{\circ}\text{C} \pm 2 \,^{\circ}\text{C}$ Operarting temperature  $+5 \,^{\circ}\text{C} .... +40 \,^{\circ}\text{C}$ 

Relative humidity 80%

Air pressure  $70...106 \, \text{kPa}$ Operating position  $106 \, \text{kPa}$ 

Operating voltage a.c. voltage, 115/230 V (+10%, -15%), 47 ... 63 Hz

Power requirement max. 20 VA (max. 20 W)

Fuses T80 L250 V (230 V), T160 L250 V (115 V)

Protection class | Lacc. to DIN EN 61010 Part 1 (VDE 0411 Part 1), 3/94 | Interference suppression | EN 55011 class B, Vfg. 1046/1984, VDE 0871 category B

nterterence suppression EN 55011 class B, Vtg. 1046/1984, VDE 08/1 category B

Dimension (in mm) 225 × 85 × 200 (W × H × D)

Mass of FG 100, abt. 1.9 kg including packing and accessories abt. 2.9 kg

#### Specifications

Frequency range 0.5 Hz ... 20 MHz

Frequency setting 4 digits

Accuracy of the frequency setting (at nominal temperature)  $\pm 0.5\%$ ,  $\pm 0.05\%$  after the automatic calibration for > 10 Hz

Duration of the auto-calibration of the frequency abt.  $0.8 \, \text{s}$  for  $f > 100 \, \text{Hz}$ , abt.  $0.8 \, \dots \, 30 \, \text{s}$  for  $f < 100 \, \text{Hz}$ 

Temperature coefficient of the frequency  $< \pm 5 \times 10^{-4}/K$ 

Time coefficient of the frequency  $< \pm 1 \times 10^{-3}/5$  min after 30 min

### Signal Output

Output impedance  $50 \Omega \pm 1.5\%$ , unsymmetrical

Output voltage  $U_{SS}$  10 mV ...  $10 \text{ V}/50 \Omega$ Max. output level incl. offset voltage  $U_{SS} + |2^*U_{offset}| \le 10.00 \text{ V}$ 

Setting of the output voltage  $U_{SS} + |Z^*U_{offset}| \le 10.00$ 

Accuracy of the output voltage f = 1 kHz  $\pm 3\%$ Additional frequency error of the output voltage  $\pm 5\%$  in the range of 10 Hz ... 100 kHz

± 10% in the range of 0.5 Hz ... 20 MHz

Temperature coefficient of the output voltage  $< \pm 5 \times 10^{-3}$ /K

d.c. voltage offset of the signal ( $U_{offset}$ )  $\pm 2.5 \text{ V}/50 \Omega$ , adjustment in 10 mV steps

Accuracy of the setting of the offset voltage  $\pm (2\% + 20 \text{ mV})$ 

Output signal sine, square, triangle, sawtooth

Nonlinear distortion factor of the sine signal < 1 % for 20 Hz ... 20 kHz, < 5% for 100 kHz ... 10 MHz

Rise time of the square signal < 15 ns
Nonlinearity of the square signal (5 ... 95%) < 1%

Adjustment of the pulse-duty factor 15 ... 85% for square and triangle 1% steps

Sweep max. 1:50, internal, digital, discrete

Sweep repetition interval 10 ms ... 60 s

## Synchronous Output

Output voltage  $U_{SS}$  5 V  $\pm$  10% at idling, pulse-duty factor abt. 1:1, CMOS compatible "Start" pulse with a width of approx. 5  $\mu$ s in the SWEEP operation

#### Display

Double-spaced alphanumeric LC display with 2 × 16 digits and background illumination. Frequency, level, units, decimal point as well as measuring functions and system messages.

#### Interface/Remote Control

FG 100 is completely remote controllable via the RS-232 C interface with 1,200 to 9,600 Bd.