

Product data sheet

Specifications



Direct online SIL starter, TeSys island, 80A AC-1, 65A AC-3, 30kW / 40hp

TPRSS065

Main

Range	TeSys
Product name	TeSys island
Device short name	TPRSS
Product or component type	SIL motor starter
Motor starter type	Direct on line
Device presentation	Direct starter connected to an automation controller through a bus coupler Operational only when connected to a bus coupler
Function available	Upstream voltage presence detection Electrical line and load protection Power and energy monitoring when connected with TPRVM voltage module Safe stop function available when connected with a TPRSM module
Product compatibility	TPRBC bus coupler TPRVM voltage interface module TPRSM SIL interface module
Poles description	3P (3 NO)
Utilisation category	AC-1 AC-2 AC-3 AC-4
Motor power kW	18.5 kW at 230 V 50 Hz (AC-3) 30 kW at 380...415 V 50 Hz (AC-3) 30 kW at 440 V 50 Hz (AC-3) 37 kW at 500 V 50 Hz (AC-3) 37 kW at 690 V 50 Hz (AC-3)
Motor power HP (UL / CSA)	5 hp at 120 V AC 60 Hz for 1 phase motors 10 hp at 240 V AC 60 Hz for 1 phase motors 20 hp at 208 V AC 60 Hz for 3 phases motors 20 hp at 240 V AC 60 Hz for 3 phases motors 40 hp at 480 V AC 60 Hz for 3 phases motors 50 hp at 600 V AC 60 Hz for 3 phases motors
[Ue] rated operational voltage	<= 690 V AC 47...63 Hz
[Ie] rated operational current	65 A (at <50 °C) at <= 440 V AC-3 80 A (at <50 °C) at <= 440 V AC-1
[Ith] conventional free air thermal current	80 A (at 50 °C)
[Ui] rated insulation voltage	690 V conforming to IEC 60947-4-1 600 V conforming to UL 60947-4-1 600 V conforming to CSA C22.2 No 60947-4-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-1
Overvoltage category	III

Thermal protection adjustment range	3.35...65 A
Thermal overload class	Class 5...30
Reset	Remotely or automatically
Irms rated making capacity	1000 A at 440 V conforming to IEC 60947
Rated breaking capacity	1000 A at 440 V conforming to IEC 60947
[Icw] rated short-time withstand current	900 A 40 °C - 1 s 520 A 40 °C - 10 s 260 A 40 °C - 1 min 110 A 40 °C - 10 min
Average impedance	1.5 mOhm - Ith 80 A 50 Hz
Power dissipation per pole	6.3 W AC-3 - Ith 65 A 9.6 W AC-1 - Ith 80 A
[Uc] control circuit voltage	24 V DC supplied by the bus coupler
Current consumption	80 mA contactor sealed 500 mA contactor closing
Power dissipation in W	20.8 W at Ie AC-3
Complementary	
Mechanical durability	6 Mcycles
Electrical durability	1.4 Mcycles 65 A AC-3 at Ue 440 V 0.5 Mcycles 80 A AC-1 at Ue 440 V
Maximum operating rate	3600 cyc/mn AC-3
Operating time	< 80 ms closing < 80 ms opening
Safety function	Safe stop: category 0 conforming to IEC 60204-1 when associated with a TPRSM module Safe stop: category 1 conforming to IEC 60204-1 when associated with a TPRSM module
Safety integrity level	SIL 2 conforming to IEC 61508 in single channel system architecture SILCL 2 conforming to IEC 62061 in single channel system architecture PL = d category 2 conforming to ISO 13849-1 in single channel system architecture
Safety performance level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Protection type	Thermal overload protection Motor overheat Overcurrent Undercurrent Jam Long start Stall Rapid cycle lockout Phase sequence Rapid restart lockout Phase reversal Phase loss Phase unbalance Ground current
Monitoring type	Time device ON Time device switch ON Number of faults Number of switching cycles Number of device power cycles Average current Iavg Average voltage Vavg Max current Imax Max voltage Vmax Active and reactive power with voltage module Active and reactive energy with voltage module True power factor with voltage module
Local signalling	1 LED (green/red) for DS (device status) 1 LED (green/red) for LS (load status)
Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product certifications	CSA UL

Mounting mode	Horizontal and vertical (35 mm symmetrical DIN rail)
Connections - terminals	EverLink BTR screw connectors 1 cable(s) 1...35 mm ² (AWG 16...AWG 2) rigid EverLink BTR screw connectors 2 cable(s) 1...25 mm ² (AWG 16...AWG 4) rigid EverLink BTR screw connectors 1 cable(s) 1...35 mm ² (AWG 16...AWG 2) flexible without cable end EverLink BTR screw connectors 2 cable(s) 1...25 mm ² (AWG 16...AWG 4) flexible without cable end EverLink BTR screw connectors 1 cable(s) 1...35 mm ² (AWG 16...AWG 2) flexible with cable end EverLink BTR screw connectors 2 cable(s) 1...25 mm ² (AWG 16...AWG 4) flexible with cable end
Tightening torque	5 N.m - cable 1...25 mm ² hexagonal 4 mm 8 N.m - cable 25...35 mm ² hexagonal 4 mm
Width	55 mm
Height	167 mm
Depth	125 mm
Net weight	1.248 kg

Environment

Ambient air temperature for storage	-25...70 °C
Ambient air temperature for operation	-10...50 °C without derating 50...60 °C with current derating
Relative humidity	5...95 %
Operating altitude	0...2000 m without derating
IP degree of protection	IP20
Pollution degree	2
Protective treatment	TC
Fire resistance	960 °C conforming to UL 94 850 °C conforming to IEC 60695-2-1 650 °C conforming to IEC 60695-2-12
Shock resistance	15 gn (duration = 11 ms) conforming to IEC 60068-2-27
Vibration resistance	1.5 mm peak to peak (f= 3...13 Hz) conforming to IEC 60068-2-6 1 gn (f= 13...200 Hz) conforming to IEC 60068-2-6
Electromagnetic compatibility	Electrostatic discharge immunity test, level 3, 8 kV air, 6 kV contact, conforming to EN/IEC 61000-4-2 Radiated RF field immunity test, level 3, 10 V/m, conforming to EN/IEC 61000-4-3 Fast transient immunity test, level 4, 4 kV, conforming to EN/IEC 61000-4-4 Surge immunity test (differential mode), level 3, 2 kV, conforming to EN/IEC 61000-4-5 Surge immunity test (common mode), level 4, 4 kV, conforming to EN/IEC 61000-4-5 Conducted RF disturbance immunity test, 20 V, conforming to EN/IEC 61000-4-6

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.321 kg
Package 1 Height	6.5 cm
Package 1 width	13.5 cm
Package 1 Length	17 cm
Unit Type of Package 2	S02
Number of Units in Package 2	8
Package 2 Weight	10.889 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
-----------------	-----------