TOSHIBA Photocoupler IRED & Photo-Transistor

TLP785, TLP785F

Office Equipment Home Electric Appliances Solid-State Relays Switching Power Supplies Contactless Controller Outputs Simplex/Multiplex Data Transmission


The TOSHIBA TLP785 consists of a silicone phototransistor optically coupled to an infrared emitting diode in a four lead plastic DIP (DIP4) with having high isolation voltage (AC: 5000 Vrms (min)). TLP785F is a lead forming type for the long creepage surface mounting of TLP785.

- TLP785: 7.62 mm pitch type DIP4
- TLP785F: 10.16 mm pitch type DIP4
- Collector-emitter voltage: 80 V (min)
- Current transfer ratio: 50% (min) Rank GB: 100% (min)
- Isolation voltage: 5000 Vrms (min)
- UL-recognized : UL 1577, File No.E67349
 - cUL-recognized :CSA Component Acceptance Service No.5A File No.E67349
- VDE-approved : EN 60747-5-5 (Note 1)
- CQC-approved: GB4943.1, GB8898 China Factory
- SEMKO-approved : EN 62368-1


Note 1 : When a VDE approved type is needed, please designate the **Option(D4)**.

Construction mechanical rating

	7.62 mm Pitch Standard Type	10.16 mm Pitch TLPxxxF Type
Creepage distance	7.0 mm (min)	8.0 mm (min)
Clearance	7.0 mm (min)	8.0 mm (min)
Insulation thickness	0.4 mm (min)	0.4 mm (min)
Inner creepage distance	4.0 mm (min)	4.0 mm (min)




Weight: 0.25 g (typ.)



Weight: 0.25 g (typ.)

Pin Configurations (top view)





- 2 : Cathode
- 3 : Emitter 4 : Collector

Start of commercial production 2010-11

Current Transfer Ratio (Note)

Туре	Classification (Note 1)	(I _C I _F = 5mA, V _{CE}	sfer Ratio (%) / I _F) = 5V, Ta = 25°C	Marking of Classification
		Min Max		
	None	50	600	Blank
	Rank Y	50	150	YE
	Rank GR	100	300	GR
	Rank BL	200	600	BL
TLP785	Rank GB	100	600	GB
	Rank YH	75	150	Y+
	Rank GRL	100	200	G
	Rank GRH	150	300	G+
	Rank BLL	200	400	В

Note 1: e.g. rank GB: TLP785 (GB)

Note: Application type name for certification test, please use standard product type name, e.g. TLP785 (GB): TLP785

Absolute Maximum Ratings (Note) (Ta = 25°C)

	Characteristics		Symbol	Rating	Unit
	Forward current		lF	60	mA
	Forward current derating (Ta ≥ 39°C)		ΔI _F / °C	-0.7	mA / °C
	Pulse forward current (No	ote 2)	IFP	1	А
LED	Power dissipation		PD	90	mW
	Power dissipation derating (Ta ≥ 39°C)		ΔP _D / °C	-0.9	mW / °C
	Reverse voltage		VR	5	V
	Junction temperature		Tj	125	°C
	Collector-emitter voltage		VCEO	80	V
	Emitter-collector voltage		V _{ECO}	7	V
tor	Collector current		IC	50	mA
Detector	Power dissipation (single circuit)		Pc	150	mW
	Power dissipation derating $(Ta \ge 25^{\circ}C)$		ΔP _C / °C	-1.5	mW / °C
	Junction temperature		Tj	125	°C
Ope	rating temperature range		T _{opr}	-55 to 110	°C
Stor	age temperature range		T _{stg}	-55 to 125	°C
Lead	d soldering temperature (10 s)		T _{sol}	260	°C
Tota	I package power dissipation		PT	240	mW
	Il package power dissipation derating ≥ 25°C)		ΔP _T / °C	-2.4	mW / °C
Isola	ation voltage (No	ote 3)	BVs	5000	V _{rms}

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note 2: Pulse Width: 100 μs or less, 100 Hz frequency

Note 3: AC, 60 s., R.H. ≤ 60%. Apply voltage to LED pin and detector pin together.

Recommended Operating Conditions (Note)

Characteristics	Symbol	Min	Тур.	Max	Unit
Supply voltage	V _{CC}	_	5	24	V
Forward current	lF	-	16	25	mA
Collector current	IC	-	1	10	mA
Operating temperature	T _{opr}	-25	_	85	°C

Note: Recommended operating conditions are given as a design guideline to obtain expected performance of the device. Additionally, each item is an independent guideline respectively. In developing designs using this product, please confirm specified characteristics shown in this document.

Individual Electrical Characteristics (Ta = 25°C)

	Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
	Forward voltage	VF	IF = 10 mA	1.0	1.15	1.3	V
LED	Reverse current	I _R	V _R = 5 V	_	_	10	μA
	Capacitance	CT	V = 0 V, f = 1 MHz	_	30	—	pF
	Collector-emitter breakdown voltage	V(BR) CEO	I _C = 0.5 mA	80		_	V
Detector	Emitter-collector breakdown voltage	V(BR) ECO	I _E = 0.1 mA	7	_	_	V
Dete	Collector dark current		V _{CE} = 24 V	_	0.01	0.1	μA
		ID(ICEO)	V _{CE} = 24 V ,Ta = 85 °C		0.6	50	μA
	Capacitance (collector to emitter)	CCE	V = 0 V, f = 1 MHz	_	6	_	pF

Coupled Electrical Characteristics (Ta = 25°C)


Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
Current transfer ratio	IF = 5 mA, VCE = 5 V		50	_	600	%
	IC / IF	Rank GE	100	_	600	70
Saturated CTR		IF = 1 mA, V _{CE} = 0.4 V	—	60	—	%
	IC / IF (sat)	Rank GB	30	-	_	70
		IC = 2.4 mA, IF = 8 mA	_	-	0.4	
Collector-emitter saturation voltage	VCE (sat)	IC = 0.2 mA, I _F = 1 mA	—	0.2	—	V
		Rank GB		_	0.4	

Isolation Characteristics (Ta = 25°C)

Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
Capacitance (input to output)	CS	V _S = 0 V, f = 1 MHz	_	0.8	_	pF
Isolation resistance	Rs	V _S = 500 V, R.H. ≤ 60 %	1×10 ¹²	10 ¹⁴	_	Ω
Isolation voltage	BVS	AC, 60 s	5000	_	_	V _{rms}

Switching Characteristics (Ta = 25°C)

Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
Rise time	tr		_	2	_	
Fall time	tf	V _{CC} = 10 V, I _C = 2 mA	_	3	_	
Turn–on time	ton	RL = 100 Ω	_	3	_	μS
Turn-off time	t _{off}		_	3	_	
Turn-on time	t _{on}		_	1.5	_	
Storage time	ts	$R_L = 1.9 k\Omega$ (fig. 1) V _{CC} = 5 V, I _F = 16 mA	_	25	_	μS
Turn-off time	toff		_	50	_	








fig. 1: Switching time test circuit


Surface-Mount Lead Form Option

TLP785(LF6)

Unit: mm







Option: Specifications for Embossed-Tape Packing; (TP6) / (TP7)


1. Applicable Package

Package Name	Product Type
DIP4LF6	TLP785
DIP4LF7	TLP785F

2. Product Naming System

Type of package used for shipment is denoted by a symbol suffix after a product number. The method of classification is as below.

(Example1)




Note: Please contact your Toshiba sales representative for details on environmental information such as the product's RoHS compatibility.


RoHS is the Directive 2011/65/EU of the European Parliament and of the Council of 8 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronics equipment.

3. Tape Dimensions

3.1 Orientation of Device in Relation to Direction of Tape Movement

Device orientation in the recesses is as shown in Figure 2.





Tape feed 🔿

Figure2 Device Orientation

3.2 Tape Packing Quantity:2000 devices per reel

3.3 Empty Device Recesses Are as Shown in Table 1.

Table1 Empty Device Recesses

	Standard	Remarks
Occurrences of 2 or more successive empty device recesses	0 device	Within any given 40mm section of tape, not including leader and trailer
Single empty device recesses	6 devices (max) per reel	Not including leader and trailer

3.4 Start and End of Tape

The start of the tape has 30 or more empty holes. The end of the tape has 50 or more empty holes.

3.5 Tape Specification

[1] TLP785(TP6) / TLP785F(TP7)

Tape material: Synthetic Resin

Dimensions: The tape dimensions are as shown in Figure 3.




Figure 3 Tape Forms		ТР6 Туре	ТР7 Туре
	А	5.1±0.1	5.05±0.1
	В	10.6±0.1	12.35±0.1
	W	16.0±0.3	24.0±0.3
	F	7.5±0.1	11.5±0.1
	Т	4.2±0.15	4.4±0.1

3.6 Reel Specification

[1] TLP785(TP6) / TLP785F(TP7)

Material: Synthetic Resin

·Dimensions: The reel dimensions are as shown in Figure 4.




Figure 4 Reel Forms

4. Packing

Two reels of photocouplers are packed in a shipping carton.


5. Label Indication

The carton bears a label indicating the product number, the symbol representing classification of standard, the quantity, the lot number and the Toshiba company name.

6. Ordering Information

When placing an order, please specify the product number, the CTR rank, the tape type and the quantity as shown in the following example.

(Example)



Note: The order code may be suffixed with a letter or a digit.

Please contact your nearest Toshiba sales representative for more details.

Note 1: Please contact your Toshiba sales representative for details on environmental information such as the product's RoHS compatibility.

RoHS is the Directive 2011/65/EU of the European Parliament and of the Council of 8 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronics equipment.

7. Soldering and Storage

7.1. Precautions for Soldering

The soldering temperature should be controlled as closely as possible to the conditions shown below, irrespective of whether a soldering iron or a reflow soldering method is used.


• When using soldering reflow

The soldering temperature profile is based on the package surface temperature.

(See the figure shown below, which is based on the package surface temperature.)

Reflow soldering must be performed once or twice.

The mounting should be completed with the interval from the first to the last mountings being 2 weeks.



	Symbol	Min	Max	Unit
Preheat temperature	Ts	150	200	°C
Preheat time	ts	60	120	5
Ramp-up rate (T _L to T _P)			3	°C/s
Liquidus temperature	TL	217		°¢
Time above TL	ել	60	150	s
Peak temperature	Τp		260	°C
Time during which T_c is between (T_P – 5) and T_P	tp		30	5
Ramp-down rate (T_P to T_L)			6	°C/s

Fig. 7.1 An Example of a Temperature Profile When Lead(Pb)-Free Solder Is Used

• When using soldering flow

Preheat the device at a temperature of 150 °C (package surface temperature) for 60 to 120 seconds. Mounting condition of 260 °C within 10 seconds is recommended. Flow soldering must be performed once.

 When using soldering Iron Complete soldering within 10 seconds for lead temperature not exceeding 260 °C or within 3 seconds not exceeding 350 °C Heating by soldering iron must be done only once per lead.

7.2. Precautions for General Storage

- Avoid storage locations where devices may be exposed to moisture or direct sunlight.
- Follow the precautions printed on the packing label of the device for transportation and storage.
- Keep the storage location temperature and humidity within a range of 5°C to 35°C and 45% to 75%, respectively.
- Do not store the products in locations with poisonous gases (especially corrosive gases) or in dusty conditions.
- Store the products in locations with minimal temperature fluctuations. Rapid temperature changes during storage can cause condensation, resulting in lead oxidation or corrosion, which will deteriorate the solderability of the leads.
- When restoring devices after removal from their packing, use anti-static containers.
- Do not allow loads to be applied directly to devices while they are in storage.
- If devices have been stored for more than two years under normal storage conditions, it is recommended that you check the leads for ease of soldering prior to use.

EN 60747-5-5 'Option: (D4)'

Attachment: Specification for <u>EN 60747-5-5</u> option: (D4)

Types: TLP785, TLP785F

Type designations for 'option: (D4) ', which are tested under EN 60747 requirements.

e.g.: TLP785(D4-GR-LF6,F	D4: EN 60747 option
	GR: CTR rank name
	LF6: standard lead bend name
	F: [[G]]/RoHS COMPATIBLE(Note 1)

Note: Use TOSHIBA standard type number for safety standard application. e.g. TLP785(D4-GR-LF6,F \rightarrow TLP785

Note 1: Please contact your Toshiba sales representative for details on environmental information such as the product's RoHS compatibility.

RoHS is the Directive 2011/65/EU of the European Parliament and of the Council of 8 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronics equipment.

Description		Symbol	Rating	Unit
Application classification				
for rated mains voltage \leq 300 V _{rms} for rated mains voltage \leq 600 V _{rms}			I–IV I–III	-
Climatic classification			55 / 115 / 21	_
Pollution degree			2	-
Maximum operating insulation voltage	TLP785	Vice	890	Vpk
	TLP785F	VIORM	1140	
Input to output test voltage, Vpr = 1.6×V _{IORM} , type and sample test t _p = 10 s, partial discharge < 5pC	TLP785		1424	Vpk
	TLP785F		1824	
Input to output test voltage, Vpr = $1.875 \times V_{IORM}$, 100% production test $t_p = 1$ s, partial discharge < 5pC	TLP785	N	1670	Vpk
	TLP785F		2140	
Highest permissible overvoltage (transient overvoltage, t _{pr} = 60s)		VTR	8000	Vpk
Safety limiting values (max. permissible ratings in case of fault) current (input current) P _{si} = 0mW power (output or total power dissipation) temperature		l _{si} Psi Ts	400 700 175	mA mW °C
Insulation resistance, V _{IO} = 500 V, Ta=25°C		Rsi	≥10 ¹²	Ω

EN 60747 Isolation Characteristics

Insulation Related Specifications

		7.62 mm pitch TLPxxx type	10.16 mm pitch TLPxxxF type
Minimum creepage distance	Cr	7.0 mm	8.0 mm
Minimum clearance	CI	7.0 mm	8.0 mm
Minimum insulation thickness	ti	0.4 mm	
Comparative tracking index	СТІ	175	

- (1) If a printed circuit is incorporated, the creepage distance and clearance may be reduced below this value. (e.g.at a standard distance between soldering eye centres of 7.5mm). If this is not permissible, the user shall take suitable measures.
- (2) This photocoupler is suitable for 'safe electrical isolation' only within the safety limit data. Maintenance of the safety data shall be ensured by means of protective circuits.


4


VDE test sign: Marking on product for EN 60747


Marking on packing for EN 60747




Marking Example: TLP785, TLP785F












TLP785,TLP785F






















NOTE: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




















NOTE: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

TLP785,TLP785F





Ambient temperature Ta (°C)



NOTE: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, and devices related to power plant. IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our website.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- GaAs (Gallium Arsenide) is used in Product. GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor. Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without
 limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile
 technology products (mass destruction weapons). Product and related software and technology may be controlled under the
 applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the
 U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited
 except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION

https://toshiba.semicon-storage.com/