

Plug with USB Charger

pro-ELEC



PEL00314



PEL00313

Specifications

Current Rating : 13A 250V AC
1 USB charging socket, Output 5V DC 1200mA
Ambient Temperature : -5°C to +40°C

Standard

BS EN 60950-1, BS 1363

Construction

Description	Material
Plug base and cover	PC
Plug pins	Brass
USB AC Adaptor PCBA	1 USB socket

Safety Specifications

Item	Conditions	Requirements
Appearance	-	No defect such as cracks, deep scratches or blemishes
Marking	-	Shall be legible and must be clear
Insulation Resistance	500 +250V DC 1 min.	Shall not be less than 5 MΩ
Dielectric strength	250 ±60V 1 min.	No damage or breakdown
Resistance to aging	70° ±5° 168 hrs.	No cracks or become sticky
Construction	20° ±5°	Complied with Figure 11,12,14, 16 gauge
Torque test	Value of 0.6N.m. (6.1kgf/cm)	Terminal, cord grip and cover screws shall withstand the torque applied
Glow Wire Test	650° / 750° electrically heated	Flame must extinguish within 30 seconds.
Temperature rise	14A 250V	Temperature rise must not exceed: 1. Line terminal : 52K 2. Accessible surface: 52K 3. Line/ Neutral pin spacer: 37K
Drop Test	25 falls at rate of 10 falls per minute.	No external damage which might affect safety and no components shall have become detached.
Live parts accessibility	Subjected to 1mm test probe with applied force of 5N when they are mounted and wired as in normal use.	Live parts of socket shall not be accessible.

Part Number Table

Description	Part Number
Plug with USB Charger, 5V DC 1.2A , Black	PEL00313
Plug with USB Charger, 5V DC 1.2A , White	PEL00314

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-ELEC