

195A.16VE | 193A-195A.VE - 1,000 Volt insulated short half-round nose pliers



Standards:

NF ISO 5745, ISO 5745, DIN ISO 5745, ASME B107.500, NF EN 60900, EN 60900, DIN EN 60900

Description:

- For your safety, all pliers are tested individually at 10,000 volts for 10 seconds, at the end of the manufacturing cycle.
- Narrow, finely serrated tips with side cutting edges. - 193A.VE: straight nose. - 195A.VE: 40° angled nose.
- Cutting edges for copper and hard steel wire to a maximum specification of 1.6mm 160 kg/mm².
- High durability carbon alloy steel, with induction hardened cutting edges.
- Bi-Material ergonomic grips resistant to chemical agents featuring: - Return spring - Tether ready (Tether point adds 10mm to nominal length)
- Varnish finish to help prevent rusting.

	195A.16VE
Diameter [mm]	2.5
Length L [mm]	160.0

Thickness E [mm]	3.0
Thickness E1 [mm]	9.0
Head Height C [mm]	50.0
Head Width B [mm]	17